

INSULATED SCREWDRIVERS

Same Klein Quality,
brand new design

 1000V

Available in
**3-Pc. &
6-Pc. Kits**

**KLEIN
TOOLS®** 



INSULATED SCREWDRIVER KITS

1000-Volt rated screwdrivers feature a layer of bright orange impact and flame resistant insulation to protect from electric shock. These screwdrivers come in different tip types and lengths, making them a must-have for any electrician's tool bag.

 1000V

3 PIECE INSULATED KIT 85073INS



6 PIECE INSULATED KIT 85076INS



1000V-rated orange impact & flame-resistant insulation provides protection from electrical shock

Meets or exceeds
ASTM F1505-16 (2021) and IEC 60900:2018

Cushion-Grip handle
for greater torque
and comfort

Tip-Ident™ quickly
identifies screwdriver tip type



Tether hole for added safety
when working at height



For Professionals
SINCE 1857™



Cat. No.	UPC 0-92644+	Tip	Type	Shank	Blade Length	Overall Length
6816INS	32917-3	3/16"		Round	6" (15.24 cm)	10.32" (26.21 cm)
6824INS	32913-5	1/4"			4" (10.16 cm)	8.32" (21.13 cm)
6826INS	32919-7	1/4"			6" (15.24 cm)	10.32" (26.21 cm)
6866INS	32920-3	5/16"			6" (15.24 cm)	11.07" (28.11 cm)
6856INS	32916-6	#1			6" (15.24 cm)	10.32" (26.21 cm)
6834INS	32914-2	#2			4" (10.16 cm)	8.32" (21.13 cm)
6836INS	32918-0	#2			6" (15.24 cm)	10.32" (26.21 cm)
6876INS	32915-9	#3			6" (15.24 cm)	11.07" (28.11 cm)
6884INS	32923-4	#1			4" (10.16 cm)	8.32" (21.13 cm)
6886INS	32924-1	#1			6" (15.24 cm)	10.32" (26.21 cm)
6844INS	32922-7	#2			4" (10.16 cm)	8.32" (21.13 cm)
6846INS	32921-0	#2			6" (15.24 cm)	10.32" (26.21 cm)

KITS	
85073INS	85076INS
UPC# 0-92644-32912-8	UPC# 0-92644-85111-7
-	•
•	•
-	-
-	-
-	•
•	•
-	•
-	-
-	-
-	-
•	-
-	•

Visit www.kleintools.com for warnings and instructions.

See our complete line of Insulated Products
www.kleintools.com



© 2022 Klein Tools, Inc.
Lincolnshire, IL 60069
MKT091222 Rev. 09/22 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

[6816INS](#) [6824INS](#) [6826INS](#) [6834INS](#) [6836INS](#) [6844INS](#) [6846INS](#) [6856INS](#) [6866INS](#) [6876INS](#) [6884INS](#)
[6886INS](#) [85073INS](#) [85076INS](#)