



Chicago® Grip - Bell-System Type L Grip



Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand. Identical to Bell-System type L strand puller. Equipped with chain, toggle and shackle. For support wire 0.134-Inch and larger, refer to 1659 series. Outside diameter of support wire includes thickness of polyethylene coating.

Specifications

Type:	Chicago Grip	Application:	Wire Pulling
Special Features:	"L" Strand Puller -- Equipped With a Chain, Toggle and Shackle	Cable Type:	Aircraft, EHS, Messenger, Guy Strand
Cable Diameter:	0.218" to 0.55" (5.54 to 13.97 mm)	Hot Latch:	N
Swing Latch:	N	Spring:	Y
Locking Handle:	Y	Jaw Type:	Double V
Jaw Length:	5" (12.7 cm)	Maximum Safe Load:	8000 lb (3629 kg)
Weight:	6.9 lb (3.12 kg)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[1684-5AT](#)