



Grip for High Strength Cable



Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand. The Chicago style grip was designed for cable sizes from 0.16-Inch to 0.55-Inch (4.06 - 13.97 mm). Double V grooves give four-point contact, reducing chance of slipping and providing proper alignment of wire and cable.

Specifications

Type:	Chicago Grip	Application:	Wire Pulling
Special Features:	Removeable file (Replacement file Cat. No. 578 and screws Cat. No. 573)	Cable Type:	Aircraft, EHS, Messenger, Guy Strand
Cable Diameter:	0.16" to 0.55" (4.06 to 13.97 mm)	Hot Latch:	N
Swing Latch:	N	Spring:	Y
Locking Handle:	Y	Jaw Type:	Single V with File Insert
Jaw Length:	5" (12.7 cm)	Maximum Safe Load:	8000 lb (3629 kg)
Weight:	6.4 lb (2.9 kg)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[1684-5F](#)