



## Chicago® Grip with Latch 0.37-Inch Cable



Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand. The Chicago style grip was designed for cable sizes from 0.12-Inch to 1.0-Inch (3.10 to 25.4 mm). Hot-line grips for both bare and insulated conductors. Grip may be placed on wire with hot-line stick. When stick is removed, latch closes automatically to guard against grip accidentally disengaging from wire. Standard hot-line grips are not supplied with springs or lock-open features.

### Specifications

Type:	Chicago Grip	Application:	Steel Stranded Cable
Special Features:	May Be Placed on Wire with Hot-Line Stick	Material:	Steel
Cable Type:	Aircraft, EHS, Messenger, Guy Strand	Cable Diameter:	0.218" to 0.55" (5.54 to 13.97 mm)
Hot Latch:	Y	Swing Latch:	N
Spring:	N	Locking Handle:	Y
Jaw Type:	Double V	Jaw Length:	5" (12.7 cm)
Maximum Safe Load:	8000 lb (3629 kg)	Weight:	6.5 lb (2.9 kg)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[1684-5H](#)