



Block and Tackle Spliced to Cat. No. 268 Block



Light, galvanized-steel shell blocks are fitted with snubbing hooks to hold the load. Sheaves are strong yet lightweight aluminum alloy with all-bronze bushings. Available with standard snap hooks or guarded snap hooks (with snap hook nose lengthened to extend over the latch or keeper).

Specifications

Overall Length:	12.096	Overall Height:	5.189
Overall Width:	4.5	Material:	Galvanized-Steel Shell Blocks, Aluminum Alloy Bushings, Nylon Rope
Hook Type:	Standard	Rope Material:	Nylon
Rope Diameter:	3/8" (9.53 mm)	Rope Length:	25'
Maximum Safe Load:	750 lb (340 kg)	Included:	268 Block; 258 Hook; 3/8" (10 mm) Diameter 25' (7.6 m) Rope
Weight:	2.8 lb (1.3 kg)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[1802-30SR](#)