



High-Leverage Side-Cutters



These Klein Tools High-Leverage Side-Cutting Pliers are made of US-made tool steel with induction hardened cutting knives for added durability. Their high-leverage design, with the rivet moved closer to the cutting edge, adds 46-Percent more gripping and cutting power. The handform handles are tempered and designed to improve durability, gripping and cutting power.

Specifications

Type:	Side Cutting Pliers	Overall Length:	9.27" (23.5 cm)
Overall Width:	2" (5.1 cm)	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.781" (2 cm)	Cut Style:	Side-Cutting
Screw Shearing:	No	Joint Type:	Hot-Riveted
Handle Color:	Black	Handle Finish:	Plain
Handle Length:	7.36" (18.7 cm)	Insulated:	No
Tether Capable:	No	Weight:	1.1 lb (0.5 kg)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[213-9NE](#)