



Ironworker's Pliers, Aggressive Knurl, 9-Inch



Klein Tools Ironworker's Pliers have aggressive teeth for a strong grip when twisting, snipping and pulling soft annealed rebar tire wire. The knurled jaws aid in easy twisting and turning. These pliers feature a hook-bend in the handle for added grip and leverage. Unique handle tempering helps absorb the "snap" when cutting wire.

Specifications

Type:	Ironworker's Pliers	Application:	Used for Rebar, High Leverage
Special Features:	Spring Loaded	Overall Length:	9.29" (23.6 cm)
Overall Width:	2.06" (5.2 cm)	Material:	Induction Hardened Steel
Nose Type:	Square	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.24" (3.1 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.781" (2 cm)	Cut Style:	Side-Cutting
Screw Shearing:	No	Joint Type:	Hot-Riveted
Handle Color:	Black	Handle Finish:	Plain
Handle Length:	7.375" (18.7 cm)	Insulated:	No
Tether Capable:	No	Weight:	1.0 lb (0.5 kg)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[213-9ST](#)