



# Ratcheting Non-Insulated Terminal Crimper, 10 to 22 AWG Wire



The full-cycle Ratcheting Crimper crimps 10-22 AWG non-insulated wire terminals. This tool features five crimping cavities in one tool for five size ranges of non-insulated terminals. Crimper design provides low effort to crimp while maintaining a high terminal pull-off force. Built-in ratchet ensures full-cycle crimping for a uniform crimp every time. Compound lever-action of narrow-span handles puts more crimping power into each squeeze. Comfort grips help reduce hand fatigue.

## Specifications

Type:	Ratcheting Crimper	Application:	Non-Insulated Terminal Crimping on Stranded Wire
Special Features:	4 Crimping Cavities	Material:	Steel
Handle Color:	Red/Black	Handle Finish:	Dual-Material
Cable Size:	10-22 AWG	Connector Type:	Non-Insulated
Overall Length:	9" (22.9 cm)	Overall Height:	0.09" (0.2 cm)
Overall Width:	3" (7.6 cm)	Weight:	1.3 lb (0.6 kg)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[3006CR](#)