



Steel Ship Auger Bit, Screw Point, 1-1/8 x 4-Inch



The deep, open-throat design of the Ship Auger bit clears chips for faster, cleaner cuts. The shank is 7/16-Inch hex to fit 1/2-Inch (13 mm) and larger three-jaw chucks. Used for heavy construction and repair work in mines, on docks and bridges as well as electrical work.

Specifications

Bit Diameter:	1-1/8" (29 mm)	Shank Diameter:	0.4"
Twist Length:	4" (10.2 cm)	Overall Length:	6" (15.2 cm)
Weight:	12.8 oz (363 g)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[53408](#)