



Insulated Screwdriver, 3/16-Inch Cabinet, 7-Inch Round Shank



Protect yourself when working near an energized source. Clearly marked with the official 1000-volt rating symbol, Klein insulated tools exceed IEC 60900 and ASTM F1505 standards for insulated tools. Two layers of insulation provide protection against electric shock. Built to handle the tough jobs with ease.

Specifications

| | | | |
|-----------------|---------------------------------|-------------------|---|
| Application: | For Work Near Energized Sources | Special Features: | Flame Retardant and Impact Resistant Handle |
| Tip Type: | Cabinet | Magnetic: | No |
| Tip Size: | 3/16" (4.8 mm) | Shank Type: | Round |
| Shank Length: | 7" (17.8 cm) | Material: | Induction Hardened Steel |
| Insulated: | Yes | Handle Material: | High-Dielectric Plastic |
| Overall Length: | 10.75" (27.3 cm) | Standard: | IEC 60900 and ASTM F1505 |
| Weight: | 2.7 oz (77 g) | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[601-7-INS](#)