



# Stubby Screwdriver, #2 Phillips, 1-1/2-Inch Round Shank



Full hollow shaft for work on stacked circuit boards or other long bolt applications. Allows for work in close quarters. Internal flanges provide solid, twist-resistant shaft anchor. Cushion-Grip™ handle allows for greater torque and comfort. Handle end is also color coded for easy identification.

## Specifications

Tip Type:	Phillips	Magnetic:	No
Tip Size:	#2	Shank Type:	Round
Shank Length:	1.5" (3.8 cm)	Material:	Steel
Insulated:	No	Handle Material:	Rubber
Handle Color:	Black	Overall Length:	3.438" (8.7 cm)
Weight:	1.6 oz (45 g)		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[603-1](#)