



Wire Bending Cabinet Tip Screwdriver 6-Inch



The 1/4 in Cabinet Tip Wire Bending Screwdriver features a heat-treated shank for durability and a flat head with a 1/4-Inch tip. The chrome plating offers excellent resistance to corrosion and provides a smooth feel. The metal stud provides a convenient way to loop, bend and connect solid wire with the installation of outlets and switches.

Specifications

Bends:	AWG Gauges Nos. 10, 12, 14	Tip Type:	Cabinet
Magnetic:	No	Tip Size:	1/4" (6.4 mm)
Shank Type:	Round	Shank Length:	6" (15.2 cm)
Material:	Steel	Insulated:	No
Overall Length:	10.344" (26.3 cm)	Weight:	4.8 oz (136 g)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[605-6B](#)