



## High-Tension Hacksaw



Klein Tools 12-Inch (30 cm) High-Tension Hacksaw has adjustable blade tension up to 30,000 Pounds Per Square Inch for fast, precise cuts. Includes 12-Inch (305 mm) x 24 Teeth Per Inch bi-metal hack saw blade and 6-Inch (152 mm) x 24 Teeth Per Inch bi-metal reciprocating saw blade. Also has convenient blade storage in handle and soft touch grips.

### Specifications

Type:	High Tension	Application:	Alternative 45 Degree Mounting for Flush Cutting
Teeth Per Inch:	24	Blade Length:	12" (30.5 cm)
Overall Length:	16.25" (41.3 cm)	Blade Material:	Bi-Metal
Throat Depth:	24	Weight:	1.5 lb (0.7 kg)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[702-12](#)