



## Cutting Crimping Pliers, Insulated, 9-Inch



These Klein Tools 9-Inch Insulated Side-Cutting Crimping Pliers offer protection against electric shock up to 1000 volts. The pliers are individually tested to exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and clearly marked with the official 1000-volt rating symbol. The pliers offer maximum strength with their forged-steel construction and a crimping die helps provide increased leverage.

### Specifications

Type:	High-Leverage Connector Crimping Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wires, Crimps Non-insulated Connectors, Lugs, and Terminals
Special Features:	Integral Guards Help Prevent Hand Contact With Conductive Parts	Overall Length:	9.68" (24.6 cm)
Overall Width:	2.49" (6.3 cm)	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.781" (2 cm)	Cut Style:	Side-Cutting
Screw Shearing:	No	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	5.73" (14.6 cm)	Insulated:	Yes
Tether Capable:	No	Standards:	IEC 60900 and ASTM F1505
Weight:	1.3 lb (0.6 kg)		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[D213-9NE-CR-INS](#)