



## Diagonal Cutting Pliers, Insulated, 7-Inch



These Insulated Diagonal-Cutting pliers have dual layered grips that are flame retardant, impact resistant, and rated for 1000-volts. They feature a tapered nose design with induction hardened cutting knives for durability. They are made of forged steel and have a hot-riveted joint for smooth action and no handle wobble.

### Specifications

Type:	Diagonal Cutting Pliers	Special Features:	Flame Retardant and Impact Resistant Handle
Overall Length:	7.67" (19.5 cm)	Material:	Induction Hardened Steel
Nose Type:	Tapered	Jaw Length:	1" (2.5 cm)
Jaw Width:	0.969" (2.5 cm)	Jaw Thickness:	0.5" (1.3 cm)
Jaw Capacity:	1.1" (2.8 cm)	Cutting Knives:	Standard
Cut Style:	Diagonal-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	4.34" (11 cm)	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight:	11.2 oz (318 g)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[D220-7-INS](#)