



Diagonal Cutting Pliers, Bell System, Skinning Holes, 6-Inch



These Klein Tools Diagonal-Cutting Pliers Bell System have a heavier design for all purpose use. The pliers' bell system type has a skinning hole for 24 AWG and W notches slit insulation cleanly. They are made of US-made steel with induction hardened cutting knives for durability. The hot-riveted joint ensures smooth action and no handle wobble.

Specifications

Type:	Diagonal Cutting Bell System Pliers	Special Features:	Skinning Hole and "W" Notches
Overall Length:	6.15" (15.6 cm)	Material:	Steel
Nose Type:	Tapered	Jaw Length:	0.696" (1.8 cm)
Jaw Width:	0.75" (1.9 cm)	Jaw Thickness:	0.813" (2.1 cm)
Jaw Capacity:	0.5" (1.3 cm)	Cutting Knives:	Standard
Knife Length:	0.594" (1.5 cm)	Cut Style:	Standard
Joint Type:	Hot Riveted	Handle Color:	Red
Handle Finish:	Plastic-Dipped	Handle Length:	3.81" (9.7 cm)
Insulated:	No	Tether Capable:	No
Weight:	5.3 oz (150 g)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[D252-6SW](#)