



9-Inch Journeyman™ Pliers Side Cutting



These Klein Tools 9-Inch Journeyman pliers are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. Their streamlined design is paired with their cross-hatched knurled jaws for confident gripping. And their unique tempered handle design, with dual material Journeyman handles provide a better grip and absorbs the snap when using their side-cutting capabilities.

Specifications

Type:	Side Cutting Pliers	Application:	General Purpose
Overall Length:	9.55" (24.3 cm)	Overall Height:	0.75" (1.9 cm)
Overall Width:	2.29" (5.8 cm)	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.781" (2 cm)	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Dark Blue/Black
Handle Finish:	Journeyman™ Dual-Material	Handle Length:	5.55" (14.1 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.1 lb (0.5 kg)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[J213-9NE](#)