



Journeyman™ Pliers Connector Crimp Side Cut 9-Inch



These Klein Tools Journeyman Pliers Connector Crimp Side Cut, have a high-leverage design, including the crimping die being placed behind the hinge. They are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. They also have cross-hatched knurled jaws and handform handles for better all around grip.

Specifications

Type:	High Leverage Side Cutting/Connector Crimping Pliers	Application:	Crimps Noninsulated Connectors, Lugs, and Terminals
Special Features:	Crimper	Overall Length:	9.55" (24.3 cm)
Overall Width:	2.29" (5.8 cm)	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.797" (2 cm)	Cut Style:	Side-Cutting
Screw Shearing:	No	Joint Type:	Hot-Riveted
Handle Color:	Yellow/Black	Handle Finish:	Journeyman™ Dual-Material
Handle Length:	5.55" (14.1 cm)	Insulated:	No
Tether Capable:	No	Weight:	1.0 lb (0.5 kg)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[J213-9NECR](#)