



Chicago Grip Hot-Line 0.31 to 0.53-Inch



The Klein S1656-30H Chicago Grip-with Hot-Line Latch for Bare Conductors is for both bare and insulated conductors. The Klein S1656-30H Chicago Grip-with Hot-Line Latch for Bare Conductors may be placed on wire with hot-line stick. When stick is removed, latch closes automatically to guard against grip accidentally disengaging from wire.

Specifications

Type:	Chicago Grip	Application:	Bare and Insulated Conductors
Special Features:	Round Inside-Jaw Contour	Cable Type:	Copper, ACSR, AAC
Cable Diameter:	0.1" to 0.53" (7.87 to 13.46 mm)	Hot Latch:	Y
Swing Latch:	N	Spring:	Y
Locking Handle:	Y	Jaw Type:	Round
Jaw Length:	4.75" (12.1 cm)	Maximum Safe Load:	4500 lb (2041 kg)
Weight:	4 lb (1.81 kg)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[S1656-30H](#)