



Chicago Grip, Forged, Hot-Line, .218 to .55-Inch



The Klein S1684-5H Chicago Grip-with Hot-Line Latch for Bare Conductors are for both bare and insulated conductors . The Klein S1684-5H Chicago Grip-with Hot-Line Latch for Bare Conductors grip may be placed on wire with hot-line stick. When stick is removed, latch closes automatically to guard against grip accidentally disengaging from wire.

Specifications

Type:	Chicago Grip	Cable Type:	Aircraft, EHS, Messenger, Guy Strand
Cable Diameter:	0.218" to 0.55" (5.54 to 13.97 mm)	Hot Latch:	Y
Swing Latch:	N	Spring:	Y
Locking Handle:	Y	Jaw Type:	Double V
Jaw Length:	5" (12.7 cm)	Maximum Safe Load:	8000 lb (3629 kg)
Weight:	6.7 lb (3.0 kg)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[S1684-5H](#)