

X5 Frequency Multiplier

RMK-5-2251+

50Ω Output 2100 to 3000 MHz

The Big Deal

- Wide bandwidth, 1500 to 2250 output
- High harmonic suppression, F4, 52 dBc; F6, 56 dBc
- Small size, 0.25 x 0.31 x 0.16"



CASE STYLE: TT1224

Product Overview

Mini-Circuits' RMK-5-2251+ frequency multiplier provides a multiplication factor of 5 converting input frequencies from 300 to 450 MHz into output frequencies from 1500 to 2250 MHz, supporting applications including synthesizers, local oscillators, satellite up and down converters and more. The unit supports input power of +17 dBm with conversion loss of 21 dB and excellent harmonic suppression. The multiplier comes housed in a miniature surface-mount package (0.25 x 0.31 x 0.16") ideal for dense circuit board layouts.

Feature	Advantages
Wide bandwidth	With an output frequency range spanning 1500-2250 MHz, this multiplier covers a wide range of applications.
Excellent harmonic suppression • F4, 52 dBc • F6, 56 dBc	Reduces spurious signals and the need for additional filtering.
Low conversion loss, 21 dB	With a low conversion loss, the unit produces higher output power signal level and less amplification may be used.
Wide input power range, +12 to +17 dBm	Wide input power signal range accommodates different input signal levels while still maintaining a low conversion loss.
Low cost	Provides an easy, cost-effective solution for generating high-frequency signals from a lower frequency signal source.
Small size	Measuring only 0.25 x 0.31 x 0.16", the RMK-5-2251+ saves space in crowded PCB layouts.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp










RMK-5-2251+

[illegible]

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

 Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

REV. A
M151107
RMK-5-2251+
ED-14926
AV/CP/AM
200813
Page 2 of 3



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[RMK-5-2251+](#)