



SYMBOL DEFINITION		
	TOTAL NO OF INSPECTIONS REQUIRED	5
	LAST NO. USED	4

MISSING SYMBOLS	
NO MISSING SYMBOL NUMBER	

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
21JN18	R	01	-	-		35191213 WAS PE394794 AND RELEASED PART DRAWING; 35191214 WAS PE394793 AND RELEASED PART DRAWING; 35191215 WAS PE377395 AND RELEASED PART DRAWING	440173	SNS	SNS	DAB
13AU18	R	02	-	-		DIM #1 WAS 32±0.15; REMOVED NOTE 5	440587	AN	SNS	DAB
08DE18	R	03	-	-		ALL PARTS - REVISED MATERIAL COLOR	441241	AN	SNS	ERM
29AU19	R	04	-	-		PARTS 35388288 AND 35381922 ADDED	445204	AN	YS	YS
25MY20	R	04	AA	-		REMOVED NO PART AVAILABLE LINE	445398	YS	YS	MA
14JN22	R	04	AB	-		ADDED 35551918 CHANGED A DIMENSIONS FOR 35381922	448279	LG	LG	AM

#### NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. PARTS SHOWN ON THIS DRAWNG USED IN ASSEMBLIES SHOWN ON TAXI 35388328 AND 35388337

3. REFERENCE MATING COMPONENTS OR EQUIVALENT: SHOWN ON TAXI 35388329 AND 35388338

4. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EANP-4-3-CS-01-EN.

6. MATERIAL RECYCLING CODE PER ISO 11469. (2)X(0.1) CHARACTERS TO BE LOCATED ON ANY EXTERIOR SURFACE.

7. FOR TOOL FIXERS, TOOL MOVEMENTS AND RE-PPAP REVIEW TOD DRAWINGS FOR CRITICAL DIMENSION. DIM #206,212,213,226,223,227, 231,233 MUST COMPLY.

35551918	01	-	POLYESTER COMPOUND NAT	2.93	19	9.4
35381922	02	-	POLYESTER COMPOUND ORG	2.863	50	12.8
35388288	01	-	POLYESTER COMPOUND GRN	2.895	40	11.3
35191213	02	-	POLYESTER COMPOUND BLU	2.943	16	7.4
35191214	02	-	POLYESTER COMPOUND GRA	2.929	25	8.9
35191215	02	-	POLYESTER COMPOUND RED	2.908	35	10.6
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOLUME (CM <sup>3</sup> )	CABLE SIZE (MM <sup>2</sup> )	A

	PROCESS SENSITIVE DIMENSION
	DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DIMENSIONAL RANGE (MM)										CHART	ET
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE ±2°											

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CM³)	DISTR CODE
SEE CHART	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE QM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	

<b>• APTIV •</b>						
CONNECTION SYSTEMS						
Anting, China						
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.						
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.						
DR	DATE					
APVD1 S. SUBRAMANIAN	21JN18					
APVD2 S. SUBRAMANIAN	21JN18					
APVD3 DARIEN AGUILAR	21JN18					
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001						
MATERIAL SEE CHART						
DRAWING NAME						
TAXI LOCK RETAINER						
DRAWING NUMBER						
35228538						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	04	AB

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[35191213](#)