





ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33344008	01	CODE A	ALL PARTS V0 / 25,1
33344013	01	CODE B	
33344014	01	CODE C	
33344017	01	CODE D	
33350438	01	CODE A	ALL PARTS NVO / 24,4
33350257	01	CODE B	
33350258	01	CODE C	
33350259	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33338835	33349754	33343453	33343455	33343476	33342253	33350062	33349758	33349757	33349770	33339449	33342247	33350092	33338837	33350047
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1



DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2	
DATE	STG	REV	N/P	CHG							
06DE18	R	01				INITIAL RELEASE			K.FAR	P.NAJ	M.GRU
15MR19	R	01	AA		B7	REFERENCE HELLERMANN TYTON DWG-NO. ADDED			K.FAR	M.GRU	K.PIT
11FE20	R	01	AB		G11 B6	PART AVAILABILITY FOR PART NUMBERS 33350438, 33350257, 33350258, 33350259 UPDATED NOTES UPDATED			P.NAJ	M.GRU	




NOTES	
-	ON MAIN VIEW ASSEMBLY 33344008 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
35269106-CUS71 - PRELIMINARY ASSEMBLY	
35269106-CUS72 - HARNESS ASSEMBLY	
35269103-CUS73 - CAR ASSEMBLY	
35269102-CUS73 - CAR ASSEMBLY	
MATING PARTS:	
- 10 WAY 1.5/2.8 MALE PANEL MOUNT ASM DWG-NO.: 35123478	
- BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CSG)	
- BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CSG)	
- PROTECTION CAP APTIV DWG-NO.: 35149888 (HT DWG-NO.: 17-2267-001-CSG)	
MATING TERMINAL SYSTEM:	
- 1.5 TERMINAL DWG-NO.: 15432214	
MAX WIRE CROSS SECTION: 1.0MM ²	
RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION:	
TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3	
SEAL: 964972-1	
MAX INSULATION CRIMP DIMENSIONS:	
HEIGHT: 3.40; WIDTH: 3.30	
- 2.8 TERMINAL DWG-NO.: 15446676	
MAX WIRE CROSS SECTION: 2.5MM ²	
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

		DIMENSIONAL RANGE (MM)										CHART E1	
☐ DIM TO CHECK	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300			
☐ DIM FOR HELP	TO	20	30	70	100	150	200	250	300	400			
TOLERANCE UNLESS OTHERWISE SPECIFIED													
☐ THEORETIC DIM		+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2			
ANGULAR TOLERANCE ±2°													

DWG TYP		DISTR CODE
PART DRAWING		
WEIGHT (GR)		D
SEE CHART		
VOLUME (CM³)		

ROUTING		
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO:		
SEE CHART		
GD&T ACCORDING TO:		
ISO 1101		
REFERENCE		
FIRST ANGLE PROJECTION		
		
DO NOT SCALE		
USE MATH DATA		



• APTIV •	
CONNECTION SYSTEMS KRAKOW, POLAND	
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA PEŁNĄ INFORMACJĘ POWIĘLANĄ, ROZPOWISZCZANĄ I WYKORZYSTYWANĄ. TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOŚCI BEZ NADANIA WYRAŹNYCH UPRAWNIEN, JEST ZABRONIONE.	
DR	K.FARON
APVD1	P.NAJDUCH
APVD2	M.GRUDZEWSKI
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNICZ PRZETWORZONE OKREŚLA APTIV 10949001	
MATERIAL	
SEE CHART	
DRAWING NAME	
10 WAY 1.5/2.8 CTCS FEMALE ASSEMBLY	
DRAWING NUMBER	
35123488	
SIZE	A1
SCALE	2:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
STG	R
REV	01
N/P	AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33344008](#)