


















3			2			1		
CWB STATUS		ZONE	REVISION HISTORY			AUTH	DR	APPROV
STO	REV		NUM	CWB				
9	R	01	-	-	RELEASED PART DRAWING	444082	EVV	EVV LJA
9	R	02	-	-	ALL PARTS - UPDATED POW ATTRIBUTES	550441	EVV	EVV LJA
20	R	03	-	-	ALL PARTS - KEY COLUMN WAS TYPE AND ADDED TORQUE VALUES NOTE	551855	HYH	JKA LJA
20	R	04	-	-	35 397987 = 0.75 WAS 2.25	551895	LXA	COO LJA

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
- DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISION REQUIREMENTS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISION TOOL PATH DATA.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLENDESSES, GATE VORTEXES, AND SOTT FLASH DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EAMP-4.3.CS.01.EN.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
- TAXI ASM CONNECTOR 35394830
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
- ASM CONNECTOR 35371764
- TORQUE VALUES TO ACHIEVE RECOMMENDED CLAMPING
VALUES ARE: 1. UNCLAMPED 2. UNCLAMPED

		(19) PROCESS SENSITIVE DIMENSION			
		DIMENSIONS EMPLOYED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)				CHART E1	
FROM	TO	> 20	> 30	> 100	> 250
		20	30	100	250
		TOLERANCE UNLESS OTHERWISE SPECIFIED			
		+0, -0.15	+0.2, -0.3	+0.4, -0.5	+0.6, -0.8
		ANGULAR TOLERANCE ±2°			

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35371057](#)