








TYPE 202
SAME AS TYPE 201
EXCEPT AS SHOWN



EXPLODED VIEW
SCALE 2:1



TYPE 201



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EXPL-4-3-CS-01-EN.

3. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

4. FOR ALL OPEN CAVITY VERSIONS SEE SHEET 1.

DRAWING NUMBER		15514557	
SIZE	SCALE	FRAME NO	SHEET NO
A1x3	4:1	2 OF 2	2 OF 2
18			

PART NO	REV	N/P	TYPE	CONNECTOR	PLR	RETAINER	SEAL CBL	USCAR OPTION	PLUGGED POSITION	BLOCKED CIRCUITS	CAVITIES
33298837	01	AC	202	15514539	15514564	15514558	15514563	A	-	X	1
35174908	01	AA	201	15514539	15514564	15514558	15514563	A	X	X	2

DIMENSIONAL RANGE (MM)				
FROM	> 0	> 20	> 30	>
TO	20	30	70	
TOLERANCE UNITS				
	±0.15	±0.2	±0.3	
ANGULAR				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33298837](#)