








TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN






TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 101



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPM-4.7-CS-01.
 - FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 - THESE ASSEMBLIES WERE DESIGNED WITHOUT CPA.
 - MAXIMUM CABLE TIE FORCE - 100N
 - DESIGNED FOR CORRUGATED TUBE NW22
 - MAXIMUM CABLE TIE WIDTH 5 MM

PART NO	REV	N/P	CONNECTOR	TYPE	CONN BODY COLOR	LOCK MECH ASST GEAR "RIGHT"	LOCK MECH ASST GEAR "LEFT"	ISL	SEAL CONN	UL94 FLAMMABILITY STANDARD
33284001	03	-	33283997	104	GRN	33284006	33284005	33284007	33207226	V-0
33284000	03	-	33283996	103	BLU	33284006	33284005	33284007	33207226	V-0
33283999	03	-	33283995	102	GRA	33284006	33284005	33284007	33207226	V-0
33283998	03	-	33283994	101	BLK	33284006	33284005	33284007	33207226	V-0
33207223	03	-	33207214	104	GRN	33207229	33207228	33207225	33207226	-
33207222	03	-	33207211	103	BLU	33207229	33207228	33207225	33207226	-
33207221	03	-	33207210	102	GRN	33207229	33207228	33207225	33207226	-
33207220	03	-	33207207	101	BLK	33207229	33207228	33207225	33207226	-

SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	36	
LAST NO. USED		44	



DWG STATUS				REVISION HISTORY				AUTH		DR		APPROV	
DATE	STG	REV	N/P	CHG	ZONE	ALL PARTS - REVISED AND RELEASED PART DRAWING	428421	RRR	RRR	RRR	RRR	RRR	RRR
150C15	R	01	-	-	-	ALL PARTS - CORRECTED DIM (7 PLCS), ADDED DIM (8 PLCS)	435304	SM	SM	SM	SM	SM	SM
06AP17	R	02	-	-	-	ALL PARTS - ADDED TYPE & CONN BODY COLOR COLUMN FROM CHART & "CORRUGATED TUBE" & "CABLE TIE WIDTH" NOTES, RENOWN UL94 FLAMMABILITY STD INSTEAD OF "REMARKS". REMOVED SEALING CODE NOTE, INSPECTION SYM #36, REVISED ASSY LABEL (1 PLCT) & ISL WAS SLD IN COLUMN AND UPDATED (PRE-STAGE) LABEL	437322	JVM	JVM	JVM	JVM	JVM	JVM
15AU17	R	03	-	-	-	ALL PARTS - UPDATED PART AVAILABILITY	440516	JMA	JMA	JMA	JMA	JMA	JMA
27JL18	R	04	-	-	-	33207220 - UPDATED PDM ATTRIBUTES	441823	JLL	JLL	JLL	JLL	JLL	JLL
17DE18	R	05	-	-	-	ALL PARTS - REVISED GRAPHICS	553487	VS	KV	VS	KV	VS	KV
04FE21	R	06	-	-	-								

CONNECTION SYSTEMS			
WARREN, IN			
COPYRIGHT 2015 APPLIED, ALL RIGHTS RESERVED.			
THIS DRAWING IS THE PROPERTY OF APPLIED AND CONTAINS APPLIED CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION BY ANY MEANS TO THIRD PARTIES, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.			
DR		DATE	
APPROV: R. RAMASWAMY	150C15		
APPROV: R. RAMASWAMY	150C15		
APPROV: TURNER, S. KEVIN	150C15		
APPROV:			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT (PCL APPL 13.10/24/2003)			
PROPERTY SEE CHART			
DRAWING NUMBER TAXI ASM CONN 26 F CTS SLD			
33207224			
SIZE A1x3	SCALE 2:1	FRAME NO 1 OF 2	SHEET NO 1 OF 1

45570533

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33283998](#)