





NOTES	
-	ON MAIN VIEW ASSEMBLY 33343722 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 10 WAY 1,5/2,8 FEMALE CONNECTOR ASM DWG-NO.: 35123488 - FIXING SLIDE APTIV DWG-NO.: 33390630 (HT DWG-NO.: 17-1487-001-CS6) - BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CS6) - BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CS6) - PROTECTION CAP APTIV DWG-NO.: 35426250 (HT DWG-NO.: 17-2272-001-CS6)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 - MAX WIRE CROSS SECTION: 1.0MM² - RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 - MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40 - 2.8 TERMINAL DWG-NO.: 13548085 - MAX WIRE CROSS SECTION: 2.5MM²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK



POSITION		1								2		3	4	
NAME		MALE HOUSING PANEL MOUNT								MALE SECONDARY LOCK		SL SEAL	FIXING SEAL	
MATERIAL		PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE	LSR 70 SHORE	
COLOR:		BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	REDDISH-BROWN	
PART-NO.:		33343470	33343472	33343487	33343489	33349766	33349772	33349773	33349774	33342244	33350073	33283927	33339919	
ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	
33343722	01	CODE A	ALL PARTS VO / 29.2	-	1	---	---	---	---	1	---	1	1	
33343766	01	CODE B		-	---	1	---	---	---	1	---	1	1	
33343767	01	CODE C		-	---	---	1	---	---	1	---	1	1	
33343773	01	CODE D		-	---	---	---	1	---	1	---	1	1	
33350430	01	CODE A	ALL PARTS NVO / 28.4	-	---	---	---	1	---	---	1	1	1	
33350431	01	CODE B		-	---	---	---	1	---	---	1	1	1	
33350432	01	CODE C		-	---	---	---	1	---	---	1	1	1	
33350433	01	CODE D		-	---	---	---	---	1	---	1	1	1	

MOUNTING BRACKET THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:		COLOR
-	PBT GF30 FR17	PBT GF30	-
1MM	33342242 / 151-02383	33350093 / 151-02382	NATURAL
1.5MM	33339586 / 151-02387	33350096 / 151-02386	GRAY
2MM	35037428	35037429	BLUE
2.5MM	33339587 / 151-02391	33350042 / 151-02390	RED
3MM	33339588 / 151-02395	33350046 / 151-02394	YELLOW
3.5MM	35037426	35037427	GRAY
4MM	35037424	35037425	GREEN



NOTE 7 (1.7)

W-W

(33.35)

48.3 ±0.5

(19.1)

NOTE 1

(WB)

NOTE 2



NOTE 3

4


1

① 39.8 +0.4 -0.65

SCALE: 1:1



DIMENSIONAL RANGE (MM)		CHART E1							
FROM	TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250
TO	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1
ANGULAR TOLERANCE ±2°									



DWG. TYPE		PART DRAWING		DISTR. CODE	
WEIGHT (GR)		SEE CHART		D	
VOLUME (CM³)					
ROUTING					
UNLESS OTHERWISE SPECIFIED					
GENERAL TOLERANCES ACCORDING TO: SEE CHART					
GD&T ACCORDING TO: ISO 1101					
REFERENCE					
FIRST ANGLE PROJECTION					
					
DO NOT SCALE					
USE MATH DATA					

• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOŚCI BEZ NADANIA WYRAŻNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	K.FARON	DATE	15MR19
APVD1	P.NAJDUCH		18MR19
APVD2	M.GRUDZEWSKI		18MR19
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKREŚLA APTIV 10949001

MATERIAL

SEE CHART

DRAWING NAME

10WAY 1,5/2,8 PANEL MOUNT MALE ASSEMBLY FOR CTCS GROUP D

DRAWING NUMBER

35123478

SIZE	A1	SCALE	2:1	FRAME NO	1 OF 1	SHEET NO	1 OF 1	STG	REV	N/P	AA
------	----	-------	-----	----------	--------	----------	--------	-----	-----	-----	----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33343766](#)