





UNWIND DIRECTION
SPULRICHTUNG

CROSS SECTION QUERSCH. MM²	CABLE LEITUNG Ø	SEAL DICHTUNG CAVITY Ø 3.60	SEAL DICHTUNG CAVITY Ø 4.00
0.35	1.20 - 1.40	15327913	15344938
0.50	1.40 - 1.60	15327913	15344938
0.75	1.70 - 1.90	15327918	15339560
1.00	1.90 - 2.10	15339412	15339560
1.50	2.20 - 2.40		10720807

X ₂ ±0.1	L ₄ ±0.2	L ₁ ±0.1	L ₂ ±0.1	L ₁ ±0.1	H ₂ ±0.2	H _{2a} ±0.2	H _{2b} ±0.2	H _{2c} ±0.2	B ₂ ±0.2	B _{2a} ±0.2	B _{2b} ±0.2	B _{2c} ±0.2	CROSS SECTION QUERSCH. MM²	VERSION
0.20	22.40	6.25	1.50	3.25	1.75	1.50	1.60		1.80	1.50	1.60		0.08-0.18	UNSEALED
0.20	22.75	6.35	2.00	2.50	2.55			1.70	2.30			1.80	0.22-0.35	
0.20	22.75	6.60	2.20	3.00	3.40			2.55	3.10			2.40	0.50-0.75	
0.20	22.75	6.60	2.20	3.00	4.00			3.35	3.75			3.10	1.00-1.50	
0.20	22.75	6.60	1.60	3.00	3.70			2.55	3.45			2.15	0.08-0.18	SEALED
0.80	22.75	6.60	1.95	3.25	4.80	1.50	1.60	5.45	1.50	1.60			0.08-0.18	
0.80	22.75	6.10	2.10	2.60	4.70			1.75	5.45			1.80	0.22-0.35	
0.80	22.75	6.60	2.10	3.00	4.70			2.55	5.45			2.40	0.50-0.75	
0.80	22.75	6.50	2.10	3.00	4.70			3.30	5.45			3.10	1.00-1.50	

WIRE-SECTION RANGE/ DRAHT-BEREICH 0.08 - 0.18 MM²



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33118034](#)