










KEY PRODUCT CHARACTERISTICS				
SAFETY/COMPLIANCE	FIT/FUNCTION	TOTAL ON DRAWING	0	
S/C CHECKPOINTS	F/F CHECKPOINTS	LAST NO. USED	0	
NO & TYPE	DESCRIPTION	RATIONALE	PTS	ZONE
16			14	



CUSTOMER PART NUMBER / FORMAT ACCORDING TO DIN 1451; 1.6 MM HIGH KUNDEN ARTIKELNUMMER / SCHRIFTART NACH DIN 1451; 1.6 MM HOCH


INDEX REPLACEMENT INSERT / FORMAT ACCORDING TO DIN 1451; 1.6 MM HIGH WECHSELEINSATZ INDEXSTEMPEL / SCHRIFTART NACH DIN 1451; 1.6 MM HOCH

TOOL CAVITY NUMBER / FORMAT ACCORDING TO DIN 1451; 1.6 MM HIGH WERKSTOFFKENNZEICHNUNG NACH VDA 260 / SCHRIFTART NACH DIN 1451; 1.6 MM HOCH



MATERIAL NAME ACCORDING TO VDA 260 / FORMAT ACCORDING TO DIN 1451; 1.6 MM HIGH WERKSTOFFKENNZEICHNUNG NACH VDA 260 / SCHRIFTART NACH DIN 1451; 1.6 MM HOCH

MANUFACTURER MARK A=2 MM HERSTELLERZEICHEN A=2 MM



TOOL CAVITY NUMBER / FORMAT ACCORDING TO DIN 1451; 1.6 MM HIGH WERKSTOFFKENNZEICHNUNG NACH VDA 260 / SCHRIFTART NACH DIN 1451; 1.6 MM HOCH


DATE INSERT SIMILAR FIRM HASCO Z 485/6/1; HAVE TO BE THE MANUFACTURING DATE DATUMSSTEMPEL AEHNLICH FA. HASCO Z 485/6/1; EINSTELLUNG MUSS DEM FERTIGUNGSDATUM ENTSPRECHEN

- REMARKS:
- PN 15494614 DRAWN
 - IN CASE OF PART MODIFICATION CHECK ASSEMBLY TOOLS AND TEST EQUIPMENT AT THE CUSTOMER AND THE SUPPLIER
 - LETTERS AND GRAVES 0.2 MM RAISED
 - MARK PLASTIC PARTS PER VDA 260
 - MATING PARTS:CONNECTOR 96 WAY DWG-NO.: 15494599

- BEMERKUNGEN:
- PN 15494614 DARGESTELLT
 - BEI ARTIKELÄNDERUNG AUF MONTAGE UND PRUEFEQUIPMENT BEIM KUNDEN SOWIE BEIM LIEFERANTEN ACHTEN
 - SCHRIFTEN UND GRAVUREN 0.2 MM ERHABEN
 - KUNSTSTOFFTEILE NACH VDA 260
 - PASSENDE GEGENSTUECKE:CONNECTOR 96 POL. DWG-NO.: 15494599


POS.	TITLE BENENNUNG	PART-NO.	PART-REV	DATE DATUM	AMOUNT ANZHL	CUSTOMER-NO.: KUNDENNUMMER	MATERIAL WERKSTOFF	RAL	NOTES REMERKUNG
A	COVER A AND LEVER A (RHD) DECKEL A UND BUEGEL A (RHD)	15494614	01	12AU04	1	---	---	---	CONDITION OF DELIVERY POS. 1+2 ASSEMBLED LIEFERZUSTAND POS. 1+2 MONTIERT
1	COVER A DECKEL A	15494600	---	---	1	---	PA6 GB20GF10 BK	9005	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
2	COVER A LEVER A BUEGEL A	15494559	---	---	1	---	PA6 GB20GF10 GY	7001	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
B	COVER B AND LEVER A (LHD) DECKEL B UND BUEGEL A (LHD)	35391994	01	04SE19	1	---	---	---	CONDITION OF DELIVERY POS. 2+3 ASSEMBLED LIEFERZUSTAND POS. 2+3 MONTIERT
3	COVER B DECKEL B	35391914	---	---	1	---	PA6 GB20GF10 BK	9005	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
2	COVER B LEVER A BUEGEL A	15494559	---	---	1	---	PA6 GB20GF10 GY	7001	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
C	COVER C AND LEVER A DECKEL C UND BUEGEL A	13530931	02	13DE06	1	---	---	---	CONDITION OF DELIVERY POS. 2+4 ASSEMBLED LIEFERZUSTAND POS. 2+4 MONTIERT
4	COVER C DECKEL C	13530928	---	---	1	---	PA6 GB20GF10 BK	9005	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
2	COVER C LEVER A BUEGEL A	15494559	---	---	1	---	PA6 GB20GF10 GY	7001	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
D	COVER D AND LEVER B (LHD) DECKEL D UND BUEGEL B (LHD)	35404805	01	15OC19	1	---	---	---	CONDITION OF DELIVERY POS. 5+6 ASSEMBLED LIEFERZUSTAND POS. 5+6 MONTIERT
5	COVER D DECKEL D	35404804	---	---	1	---	PA6 GB20GF10 BK	9005	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
6	COVER D LEVER B BUEGEL B	35410499	---	---	1	---	PA6 GB20GF10 NAT	---	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
E	COVER E AND LEVER B (RHD) DECKEL E UND BUEGEL B (RHD)	35426589	01	10DE19	1	---	---	---	CONDITION OF DELIVERY POS. 6+7 ASSEMBLED LIEFERZUSTAND POS. 6+7 MONTIERT
7	COVER E DECKEL E	35426580	---	---	1	---	PA6 GB20GF10 BK	9005	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
6	COVER E LEVER B BUEGEL B	35410499	---	---	1	---	PA6 GB20GF10 NAT	---	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
F	COVER B AND LEVER B (LHD) DECKEL B UND BUEGEL B (LHD)	35435642	01	14JA20	1	---	---	---	CONDITION OF DELIVERY POS. 3+6 ASSEMBLED LIEFERZUSTAND POS. 3+6 MONTIERT
3	COVER B DECKEL B	35391914	---	---	1	---	PA6 GB20GF10 BK	9005	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR
6	COVER B LEVER B BUEGEL B	35410499	---	---	1	---	PA6 GB20GF10 NAT	---	ONLY ASSEMBLED PARTS AVAILABLE NUR MONTIERT LIEFERBAR

3	DWG STATUS DATE	STG	REV	IN	PLCHS	ZONE	2	REVISION HISTORY	1	APVD 1	APVD 2
12AU04	R	01	--					INITIAL RELEASE / ERSTFREIABE		T.SWIE	M.SKR
24W05	R	02	--			08		VARIANT COVER B / C AND LEVER A ADDED VARIANTE DECKEL B / C UND BUEGEL A HINZU		T.SWIE	M.SKR
13DE06	R	03	--			E10		COVER B AND C LOCKING LATCH MODIFIED DECKEL B UND C LASHENEN MODIFIZIERT		M.HOR	MICHA.
04SE19	R	04	--			M7		PN 35391994 WAS / WAR PN 13530930 PN 35391914 WAS / WAR PN 13530926 COVER B NEW CAMS ADDED / HINZU DRAWING FORMAT UPDATED / ERNEUERT		T.MAZ	O.HAC
15OC19	R	05	--			E15A8		PN 35404805 ADDED/ HINZU PN 35404804 ADDED/ HINZU PN 35410499 (LEV B) ADDED/ HINZU OVERALL REVISED/ VERANDERUNG GEGENSTANDT COVER D WITH MODIFIED LOCKING/ DECKEL D MIT MODIFIZIERTER VERRIEGELUNG		R.WOL	O.HAC
11DE19	R	06	--			KBW02		PN 35426589 ADDED/ HINZU PN 35426580 (COV E) ADDED/ HINZU REVISED LOCKING/ VERANDERTE VERRIEGELUNG PN 35410499 (LEV B) ADDED/ HINZU		C.ELI	O.HAC
15JA20						KB12		PN 35435642 ADDED/ HINZU TITLE REVISED/ BEZEICHNUNG ERGAENZT; REMARKS ADDED/ BEMERKUNGEN ERGAENZT; DIM./MASS (48.7) WAS/ WAR (48.5); REMARKS REVISED/ BEMERKUNGEN VERARBEITET; PN 15494614 DRAWN ADDED/ DARGESTELLT HINZU		C.ELI	O.HAC



DEFORMATION PERMISSIBLE EINFALL ZULAESSIG

SCALE / MASSTAB: 1:1



DWG. TYPE PART DRAWING	DISTR. CODE
REV. 01/19.0	D
VOLUME 10/1	
ROUTING	

GENERAL TOLERANCES ACCORDING TO:	SEE CHART / SIEHE TABELLE
GD&T ACCORDING TO:	150 1101

REFERENCE	FIRST ANGLE PROJECTION

DO NOT SCALE	USE MATH DATA

•APTIV•

CONNECTION SYSTEMS
D-42119 WUPPERTAL
COPYRIGHT 2004 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS CONTENTS TO OTHERS, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DATE	11AU04
DR	T.SWIE
APVD1	STOR.
APVD2	M.SKR
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (KOHREKT) POTENTIAL GEFÄHRLICHE STOFFE UND REZYKULANTEILE (GEMÄSS APTIV (KOHREKT))	
MATERIAL	

SEE CHART / SIEHE TABELLE

DRAWING NAME
COVER AND LEVER FOR CONNECTOR 96 WAY
DECKEL UND BUEGEL FUER CONNECTOR 96 POL.

DRAWING NUMBER	15494615
SIZE	A0
SCALE	2:1
FRAME NO	1
SHEET NO	1
OF	1
STG	R
REV	06
NVP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15494614](#)