








MISSING SYMBOLS		DWG STATUS		ZONE		REVISION HISTORY		AUTHOR		REV	
NO	MISSING SYMBOL NUMBER	DATE	TYPE	BY	CHKD	ZONE	DESCRIPTION	DATE	BY	CHKD	REV
27	27A15	R	01	-	-	-	ALL PARTS - CREATED PART DRAWING	427871	KV	SVS	01
25	25E15	R	02	-	-	-	33211199-02- RELEASED PART DRAWING	430423	KV	KVS	02
20	20A.16	R	03	-	-	-	REVISED GRAPHICS	433565	SM	SM	03
16	16E617	R	04	-	-	-	ALL PARTS- ADDED CORRUGATED TUBE & "CABLE TIE WIDTH" NOTES, CONN BODY CORN COLUMN AND REMOVED ULTRA FLAMMABILITY COLUMN	432728	JVM	JVM	04
16	16A018	R	05	-	-	-	ALL PART - REVISED DIM #36 33211199 - UPDATED PART AVAILABILITY	441624	KRK	KRK	05
24	24A119	R	06	-	-	-	33213201 - UPDATED PART AVAILABILITY	443727	DL	SNS	06
6	620C19	R	07	-	-	-	33213200 - UPDATED PART AVAILABILITY	550166	JAM	JAM	07
3	3A0A20	R	08	-	-	-	33276719 - UPDATED PART AVAILABILITY	550918	LO	JAM	08



- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED UP FOR COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOR MARKS, COLOR
BLEMISHES, GATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EAMP-4-3.CS.01-EN
 3. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 4. DESIGNED FOR CORRUGATED TUBE NIK62
 5. MAXIMUM CABLE TIE WIDTH 5 MM

31267422	02	AB	104	31267618	BLUE	31267623	31273174	3119869	V-0
31267421	02	AB	103	31267617	BLUE	31267623	31273174	3119869	V-0
31267420	02	AB	102	31267616	BLACK	31267623	31273174	3119869	V-0
31267419	02	AC	101	31267615	GRAY	31267623	31273174	3119869	V-0
31213232	02	AB	104	31213197	GREEN	31213192	31213193	3119869	-
31213201	02	AC	103	31213196	BLUE	31213192	31213193	3119869	-
31213200	02	AC	102	31213195	GRAY	31213192	31213193	3119869	-
31213199	02	AB	101	31213194	BLACK	31213192	31213193	3119869	-
PART NO	REV	N/P	TYPE	CONN	CONN BODY COLOR	INNER CONN	LOCK SLC	SEAL CONN	UL94 FLAMMABILITY STD

DIMENSIONAL RANGE (MM)		CHART									
FROM	TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
		+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2	

1. LINE DRAWING THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. 2. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. 3. CONTACT APPLICATOR SALES TO ASSURE AVAILABILITY OF PARTS.	
DRG TYPE: PART DRAWING	
STYLE	DISTR CODE
VOLUME (PARTIAL)	D
(UNLESS OTHERWISE SPECIFIED) THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M (1994) AS AMENDED BY THE 2003 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM (2003). SEPARATE PATTERNING OF FEATURES MAY BE REQUIRED SEPARATELY. RELEVANCE OF DATA REMAINS.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE:	
THIRD ANGLE PROJECTION	DO NOT SCALE
	USE WITH DATA
	

• APTIV • CONNECTION SYSTEMS Chennai, India COPYRIGHT 2010 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. IT IS TO BE USED FOR THE DESIGN AND UTILIZATION OF THE COMPONENTS OR TO REPLICATE SUCH DATA, AS WELL AS COMMUNICATE SUCH INFORMATION TO ANY OTHER PARTY WITHOUT APTIV'S AUTHORIZATION. IT IS PROHIBITED.									
DATE									
DR									
APPROV V. KANDASAMY						24AP15			
APPROV V. KANDASAMY						24AP15			
APPROV TURNER KEVIN S						27AP15			
APPROV									
SUBSTANCES OF CONSUMERS AND RECYCLED CONTENT PER APTIV [1094060]									
MATERIAL SEE CHART									
DRAWING NAME TAXI ASM CONN 62 M CTS SLD									
DRAWING NUMBER 33213203									
SIZE A1x3	SCALE 2:1	DATE 02/2	FRAME 02	SHEET NO 1 OF 1	SHEET NO 8	SHEET NO 8	SHEET NO 8	SHEET NO 8	SHEET NO 8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33213200](#)