







TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 4:1




TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 4:1




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 4:1





TYPE 106
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 4:1






TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN
SCALE 4:1




TYPE 101



EXPLODED VIEW
SCALE 2:1



SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF INSPECTIONS REQUIRED	28	NO MISSING SYMBOL NUMBER
	LAST NO. USED		

21

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - PART IS MANUFACTURED TO GEOMETRIC TOLERANCES. CENTERLINE DIMENSIONS ARE FOR REFERENCE ONLY.
 - SEALING CODE 4 - DESIGN WILL MEET REQUIREMENTS OF SAE/USCAR-2 CONNECTOR SYSTEM ENVIRONMENTAL TEST FLOWCHART (PRESSURE/VACUUM AND SUBMERSION).
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMMISHES, GATE VESTIGES, AND SPOKE FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EIAJ-4-1.3C.01.1EN.
 - FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 - ASSEMBLY TO BE USED WITH APPROPRIATE APTIV HOLDER DESIGN.
 - ASSEMBLY TO BE PROCESSED USING APTIV CONNECTION SYSTEMS BEST PRACTICE METHODS AND/OR CONNECTOR ASSEMBLY INSTRUCTIONS AND APPLICABLE REPAIR PROCEDURES.
 - BEFORE TERMINAL ASSEMBLY, VERIFY THAT PLR IS IN THE PRE-STAGE POSITION ON THE CONNECTOR. IF NOT, RETURN PLR TO PRE-STAGE POSITION.
 - FOR DIFFERENT PUNCH PATTERN CONFIGURATIONS (IF AVAILABLE) SEE SHEET 2.
 - FOR ASSEMBLIES WITHOUT CPA SEE DRAWING 15532382.

PART	NO	REV	N/P	TYPE	CONNECTOR	PLR	SEAL CONN	SEAL CBL	RETAINER	CPA	USCAR OPTION
15513509	05	A6	106	15513502	15513516	15513518	15513515	15513512	15519096	F	
15513508	05	A6	105	15513501	15513516	15513518	15513515	15513512	15519096	E	
15513507	05	AH	104	15513500	15513516	15513518	15513515	15513512	15519096	D	
15513506	05	AH	103	15513499	15513516	15513518	15513515	15513512	15519096	C	
15513505	05	AJ	102	15513498	15513516	15513518	15513515	15513512	15519096	B	
15513504	05	A6	101	15513497	15513516	15513518	15513515	15513512	15519096	A	

DRAWING NUMBER 15513510									
SIZE A1x3	SCALE 5:1	FRAME NO 2 OF 2	SHEET NO 1 OF 2	REV R 19					

UNLESS OTHERWISE SPECIFIED DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED									
FUNCTIONAL PARTS (MM)	TO	20	25	30	35	40	45	50	55
TO	20	25	30	35	40	45	50	55	60
TOLERANCE UNLESS OTHERWISE SPECIFIED									
15513510	15513511	15513512	15513513	15513514	15513515	15513516	15513517	15513518	15513519
ANGULAR TOLERANCES									

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA		
---------------------------	-----------------	------------------	--	--

• APTIV •				
CONNECTION SYSTEMS				
WHEN IN COPYRIGHT 2013 APTIV. ALL RIGHTS RESERVED.				
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION BY ANY MEANS TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.				
DATE	DATE			
DR APPROV HECTOR CLAUDIO 11JAI13	10JAI13			
APPROV GERARDO GOMEZ L. 11JAI13	10JAI13			
APPROV				
SUBSTANCES OF CONCERN AND RECYCLED CONTENT (PUL) APTIV (1504900)				
REPAIR SEE CHART				
OPERATING NAME TAXI ASM CONN 6 F CCS 1.5 SLD				
DRAWING NUMBER 15513510				
SIZE A1x3	SCALE 5:1	FRAME NO 1 OF 2	SHEET NO 1 OF 2	REV R 19

012213210

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15513505](#)