







[illegible]






ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL WEIGHT
33342293	01	CODE A	ALL PARTS V0 / 37,5
33342294	01	CODE B	
33342295	01	CODE C	
33342300	01	CODE D	
33347872	01	CODE A	ALL PARTS NVO / 36,45
33349684	01	CODE B	
33349686	01	CODE C	
33349700	01	CODE D	

B		7				6				5				4			
POSITION	1									2				3		4	
NAME	HOUSING PANAL MOUNT									SECONDARY LOCK				SL SEAL		FIXING SEAL	
MATERIAL	PBT GF30 FR17					PBT GF30				PBT GF30 FR17		PBT GF30		LSR 50 SHORE		LSR 70 SHORE	
COLOR:	BLACK	BLACK	GREY	GREEN	BLUE	BLACK	GREY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	REDDISH-BROWN				
PART-NO.:	33325410	33325411	33325411	33325409	33325408	33347504	33347890	33347866	33347871	33325395	33347487	33283927	33283924				
-	---	---	---	---	---	---	---	---	---	---	---	---	---				
-	1	---	---	---	---	---	---	---	---	1	---	1	1				
-	---	---	1	---	---	---	---	---	---	1	---	1	1				
-	---	---	---	1	---	---	---	---	---	1	---	1	1				
-	---	---	---	---	1	---	---	---	---	1	---	1	1				
-	---	---	---	---	---	1	---	---	---	---	1	1	1				
-	---	---	---	---	---	---	1	---	---	---	1	1	1				
-	---	---	---	---	---	---	---	---	1	---	1	1	1				
-	---	---	---	---	---	---	---	---	1	---	1	1	1				
-	---	---	---	---	---	---	---	---	---	---	1	1	1				

1			2				3		
DWO STATUS			REVISION HISTORY				DR		
DATE	STG	REV	CHG			AUTH	APVD 1	APVD 2	
28NOV19	R	01	AA			INITIAL RELEASE	A.RAJ	P.NAJ.W.GRU	
15MR19	R	01	AA	L14 F12		PROTECTION HELLOWMAN TYTON DRAG, ADOED REFERENCE HELLOWMAN TYTON DRAG, ADOED	K.FAR	W.GRU.K.PIT M	
27OC20	R	01	AB	L14 L9 K14		PROTECTION CAP APVD DNO IS: 55462944 DWS: 55247000 PART AVAILABILITY FOR PART NUMBERS 33348782, 33348814, 33348906, 33349000 NOTES UPDATED	P.NAJ	W.GRU.W.SKR	




① MOUNTING BRACKET THICKNESS	FIXING SLIDE ACTIV/VHT PART-NO. 4		COLOR
	PBT GF30 FR17	PBT GF30	
-	33366500	33366507	NATURAL
1.5MM	33341425 / 151-02405	33348137 / 151-02404	GREY
2MM	33366509	33366506	BLUE
2.5MM	33283296 / 151-02409	33348133 / 151-02408	RED
3MM	33325396 / 151-02413	33348135 / 151-02412	YELLOW
3.5MM	33314244 / 151-02417	33348136 / 151-02416	GREEN
4MM	33366510	33366505	GREEN



		SHAFT CURRENT TOLERANCE										CHART E	
☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
☐ DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED												
☐ THEORETIC DIM	ANGULAR TOLERANCE		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
		5	4										

SCALE
[1 : 1]



18 MAY 1,5
CTCS PANEL MOUNT MALE ASSEMBLY

• APT IV •

NO. 117
PART DRAWING

WEIGHT (G)
SEE CHART

VOLUME (CM³)

ROUTING

DISTR CODE

D

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV, ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION, OR
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL
AS COMMUNICATION OF AND CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEJ WŁASNOŚCIĄ APTIV I ZAWIERA POŁICNE
INFORMACJE, POWIĘLANE, ROZPOWISZCZANIANE I WYKORYSTYWANIE TEJ
DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH (JAKI) JAKOŚĆI PRZESYŁANYCH
INNYM JAKIEKOLWIEB KANALIZACJĄ, BEZ NAJADNIA WYRAŻONYCH
UPRAWNIENI, JEJ ZABRONIŁO.

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:

SEE CHART

GD&T
ACCORDING TO:

ISO 1101

DATE

DR	A. RAJEEV	27NO18
APVD1	P. NAJDUCH	28NO18
APVD2	M. GRUDZEWSKI	29NO18
APVD3		
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (DPAH001)
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKREŚLA
APTIV (DPAH001)

REFERENCE

FIRST ANGLE PROJECTION




DO NOT
SCALE

USE MATH
DATA





MATERIAL

SEE CHART

DRAWING NAME

DRAWING NUMBER

35195557

SCALE

1 OF 1

SHEET NO

1 OF 1

REV

R 01

APV

AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33342294](#)