


DRAWING NUMBER NUMERO DISEGNO	<b>FSC 309133</b>	REVISION REVISIONE	<b>C</b>	SHEET FOGLIO	<b>1/2</b>	APPROVAL LEVEL LIV. DI APPROVAZIONE	-
DRAWING DISEGNO	<b>C</b>						


18-13475	02-02-2018	C	4E SH2	Added new colours	FG		GI
14-06120	03-06-2014	B	-	UPDATED FORMAT AND ADDED DELPHI PART NUMBERS	FG		MC
14-03142	05-03-2014	A	A5 SH1	Added pn 33403915-33403916-33403917	GB	FG	MC
21-2006	13-03-2006	13	-	Added new PN	FG		MC
02-2006	13-01-2006	12	-	Changed the raw material housing	FG	EC	MC
ECN-NO. NUMERO ECN	DATE DD/ MM / YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY DISEGNATORE	CHK. BY CONTROLLATO	APPR. BY APPROVATO

PRODUCT SPEC. SPEC. DI PRODOTTO		PACKAGING SPEC. SPEC. DI IMBALLAGGIO		APPLICATION SPEC. SPEC. DI APPLICAZIONE		COPYRIGHT APTIV CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF APTIV CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.				QUESTO DISEGNO E' 'PROPRIETA' DI APTIV CORPORATION E CONTIENE INFORMAZIONI CONFIDENZIALI. LA RIPRODUZIONE, DISTRIBUZIONE E UTILIZZAZIONE DI QUESTO DOCUMENTO O DELLE SUE RELATIVE MATEMATICHE CAD, NONCHE LA COMUNICAZIONE DI QUALSIASI CONTENUTO AD ALTRI, SENZA ESPLICITA AUTORIZZAZIONE, E' PROIBITA					
TOLERANCES TOLLERANZE		± 0.3mm / ± 2°		MATERIAL : MATERIALE :		SURFACE FINISH FINITURA SUPERFICIALE		• APTIV •				CAD SYSTEM			
COUNTERPART Nr. CONTROPARTE Nr.				PBT GF 15% SEE TABLE		-		pro / eng							
DO NOT SCALE DRAWING DISEGNO FUORI SCALA				COLOUR : COLORE :		SEE TABLE		C		 ISO PROJECTION PROIEZIONE ISO		DIMENSION IN MILLIMETERS DIMENSIONI IN MILLIMETRI		DWG SIZE FORMATO A3	
				TOOL NO. -		LOC. CODE NAZIONALITA' IT		DRAWING NUMBER NUMERO DISEGNO				SHEET FOGLIO			
DRAWN BY DISEGNATORE		DATE DATA		NAME NOME		TITLE DESCRIZIONE		FSC 309133				1 of 1 di			
CHECKED BY CONTROLLATO		13-01-06		GIRARD		24 WAY REAR DOOR TO BODY ( PBT VERSION )						2			
APPROVED BY APPROVATO		13-01-06		COLOMBO		ESR NO. NUMERO ESR		CAT. NO. NUMERO CAT.		FILE NAME NOME FILE				SCALE SCALA	
						-		SEE TABLE		FSC 309133				2:1	


DESIGNATED CHARACTERISTICS				QCI	KPC
	LAST NO USED			CI	FF
1	TOTAL ON DRAWING	SAFETY/COMPLIANCE		SC	SC
QCI	KCP				

DRAWING NUMBER NUMERO DISEGNO	<b>FSC 309133</b>	REVISION REVISIONE	<b>C</b>	SHEET FOGLIO	<b>2/2</b>	APPROVAL LEVEL LIV. DI APPROVAZIONE
DRAWING DISEGNO	<b>C</b>					

TYPE	MVL P/Ns	REV	DELPHI P/Ns	REV	COLOR
SEALED VERSION 24w OPEN	HCCMHPE24BKAFSV ( 24W Version )	A	33500427	01	BLACK
	-	A	33403915	01	NATURAL
	-	A	33403916	01	GREEN
	-	A	33403917	01	ORANGE
	-	A	35163344	01	Dark Blue
	-	A	35163354	01	Red
	-	A	35163352	01	Light Brow
	-	A	35163353	01	Light Gree
	-	A	35163355	01	Purple
SEALED-12w OPEN	1726 12.06 ( 12W Version )	A	13593552	01	BLACK
UNSEALED VERSION	HCCMHPE24BKAF	A	33500426	01	BLACK



SCALE 1:1



DETAIL J  
SCALE 5:1




[illegible]

SCALE 1:1

UNSEALED VERSION  
NO CLOSED WAYS

SEALED VERSION  
NO CLOSED WAYS

SEALED VERSION  
12 CLOSED WAYS:  
A2, A3, A4, A5, A6, A7  
C2, C3, C4, C5, C6, C7






SECTION F-F




CAR FLOOR

K

CONNECTOR INSERTION SIDE — 

No burrs allowed along all the cut perimeter

<b>18-13475</b>	<b>02-02-2018</b>	<b>C</b>	<b>4E SH2</b>	<b>Added new colours</b>		<b>FG</b>		<b>GI</b>
<b>14-06120</b>	<b>03-06-2014</b>	<b>B</b>	<b>-</b>	<b>UPDATED FORMAT AND ADDED DELPHI PART NUMBERS</b>		<b>FG</b>		<b>MC</b>
<b>14-03142</b>	<b>05-03-2014</b>	<b>A</b>	<b>A5 SH1</b>	<b>Added pn 33403915-33403916-33403917</b>		<b>GB</b>	<b>FG</b>	<b>MC</b>
<b>21-2006</b>	<b>13-03-2006</b>	<b>13</b>	<b>-</b>	<b>Added new PN</b>		<b>FG</b>		<b>MC</b>
<b>02-2006</b>	<b>13-01-2006</b>	<b>12</b>	<b>-</b>	<b>Changed the raw material housing</b>		<b>FG</b>	<b>EC</b>	<b>MC</b>
ECN-NO. NUMERO - ECN	DATE DD / MM / YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA		DRAWN BY DISEGNATORE	CHK. BY CONTROLLATO	APPR. BY APPROVATO
PRODUCT SPEC. SPEC. DI PRODOTTO	PACKAGING SPEC. SPEC. DI IMBALLAGGIO	APPLICATION SPEC. SPEC. DI APPLICAZIONE	COPYRIGHT - APTIV CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF APTIV CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED. QUESTO DISEGNO E' PROPRIETA' DI APTIV CORPORATION E CONTIENE INFORMAZIONI CONFIDENZIALI. LA RIPRODUZIONE, DISTRIBUZIONE E UTILIZZAZIONE DI QUESTO DOCUMENTO O DELLE SUE RELATIVE MATEMATICHE CAD, NONCHE LA COMUNICAZIONE DI QUALSIASI CONTENUTO AD ALTRI, SENZA ESPlicita AUTORIZZAZIONE, E' PROIBITA					
TOLERANCES TOLLERANZE		MATERIAL : MATERIALE :		SURFACE FINISH FINITURA SUPERFICIALE				CAD SYSTEM
COUNTERPART Nr. CONTROPARTE Nr.		PBT GF 15%		-				pro / eng.
DO NOT SCALE DRAWING DISEGNO FUORI SCALA		COLOUR : COLORE :		LOC. CODE NAZIONALITA' IT				DWG SIZE FORMATO
DATE DATA		TITLE DESCRIZIONE		DRAWING NUMBER NUMERO DISEGNO		DIMENSION IN MILLIMETERS DIMENSIONI IN MILLIMETRI		A3
NAME NOME		24 WAY REAR DOOR TO BODY ( PBT VERSION )		FSC 309133		SHEET FOGLIO		
DRAWN BY DISEGNATORE		24		FSC 309133		2		
CHECKED BY CONTROLLATO		CINI		FSC 309133		di		
APPROVED BY APPROVATO		COLOMBO		FSC 309133		2		
ESR NO. NUMERO ESR		SEE TABLE		FILE NAME NOME FILE		SCALE SCALA		2:1

DESIGNATED CHARACTERISTICS							QCI	KPC
		LAST NO USED					 CI	 FF
	1	TOTAL ON DRAWING	SAFETY/COMPLIANCE					 SC
QCI	KCP							

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35163353](#)