





ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33340130	01	CODE A	ALL PARTS V0 / 26,1
33339571	01	CODE B	
33340234	01	CODE C	
33340235	01	CODE D	
33350122	01	CODE A	ALL PARTS NVO / 25,3
33350276	01	CODE B	
33350334	01	CODE C	
33350335	01	CODE D	


POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33338835	33349754	33338899	33338897	33338900	33338903	33350053	33350055	33350054	33349767	33339449	33338904	33350081	33338837	33350047
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1



DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
15MR19	R	01				INITIAL RELEASE		K.FAR	P.NAJ	M.GRU
11FE20	R	01	AA		G11 A7	PART AVAILABILITY FOR PART NUMBERS 33350122, 33350276, 33350334, 33350335 UPDATED NOTES UPDATED		P.NAJ	M.GRU	




NOTES	
-	ON MAIN VIEW ASSEMBLY 33340130 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
35269106-CUS71 - PRELIMINARY ASSEMBLY	
35269106-CUS72 - HARNESS ASSEMBLY	
35269103-CUS73 - CAR ASSEMBLY	
35269102-CUS73 - CAR ASSEMBLY	
MATING PARTS:	
- 12 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35123474	
- BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CS6)	
- BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CS6)	
- PROTECTION CAP APTIV DWG-NO.: 35149888 (HT DWG-NO.: 17-2267-001-CS6)	
MATING TERMINAL SYSTEM:	
- 1.5 TERMINAL DWG-NO.: 15432214	
MAX WIRE CROSS SECTION: 1.0MM ²	
RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION:	
TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3	
SEAL: 964972-1	
MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.30	
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

		SHARP CORNER TOLERANCE									
DIM TO CHECK	DIMENSIONAL RANGE (MM)										CHART E1
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
1) DIM FOR HELP	TO	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	
ANGULAR TOLERANCE ±2°											



DWG. TYPE		DISTR. CODE
PART DRAWING		
WEIGHT (GR)	SEE CHART	
VOLUME (CM ³)	---	
ROUTING		
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO:		
SEE CHART		
GD&T ACCORDING TO:		
ISO 1101		
REFERENCE		
FIRST ANGLE PROJECTION		
		
DO NOT SCALE		
USE MATH DATA		
		



• APTIV •	
CONNECTION SYSTEMS KRAKOW, POLAND	
COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWYSZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOŚCI, BEZ NADANIA WYRAŻNYCH UPRAWNIEN, JEST ZABRONIONE.	
DR	K.FARON
APVD1	P.NAJDUCH
APVD2	M.GRUDZEWSKI
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001	
MATERIAL	
SEE CHART	
DRAWING NAME	
12 WAY 1.5 CTCS FEMALE ASSEMBLY	
DRAWING NUMBER	
35123477	
SIZE	A1
SCALE	2:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
STG	R
REV	01
N/P	AA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33340235](#)