





NOTES	
-	ON MAIN VIEW ASSEMBLY 33341408 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 8 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 35153960 - FIXING SLIDE APTIV DWG-NO.: 33294397 (HT DWG-NO.: 17-1458-001-CSG) - BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35428682 (HT DWG-NO.: 17-2271-001-CSG)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1,0MM ² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1,5MM ² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT








ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33341408	01	CODE A	ALL PARTS VO / 24,05
33341409	01	CODE B	
33341410	01	CODE C	
33341411	01	CODE D	
33346266	01	CODE A	ALL PARTS NVO / 23,4
33347518	01	CODE B	
33347519	01	CODE C	
33347530	01	CODE D	

NOTES	
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK

POSITION	1				2		3	4
NAME	HOUSING PANAL MOUNT				SECONDARY LOCK		SL SEAL	FIXING SEAL
MATERIAL	PBT GF30 FR17				PBT GF30 FR17		LSR 50 SHORE	LSR 70 SHORE
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE
PART-NO.:	33338796	33338794	33338798	33338831	33344887	33347334	33347333	33347308
-	---	---	---	---	---	---	---	---
-	1	---	---	---	---	---	---	---
-	---	1	---	---	---	---	---	---
-	---	---	1	---	---	---	---	---
-	---	---	---	1	---	---	---	---
-	---	---	---	---	1	---	---	---
-	---	---	---	---	---	1	---	---
-	---	---	---	---	---	---	1	---
-	---	---	---	---	---	---	---	1



MOUNTING BRACKET THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:	COLOR
-	PBT GF30 FR17 PBT GF30	-
1MM	35065351 35065358	NATURAL
1.5MM	35065364 35065366	GRAY
2MM	35065367 35065368	BLUE
2.5MM	33282490 / 151-02370 33344869 / 151-02371	RED
3MM	33341422 / 151-02374 33344870 / 151-2375	YELLOW
3.5MM	33341423 / 151-02378 33344871 / 151-02379	GRAY
4MM	35065369 35065353	GREEN



		TYPICAL CORNER TOLERANCE								CHART E1
DIM TO CHECK	DIMENSIONAL RANGE (MM)									
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
DIM FOR HELP	TO	20	30	70	100	150	200	250	300	400
	TOLERANCE UNLESS OTHERWISE SPECIFIED									
THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
UNLESS OTHERWISE SPECIFIED										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33341410](#)