


- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. SEALING CODE 4 - DESIGN WILL MEET REQUIREMENTS OF SAE/USCAR-2
CONNECTOR SYSTEMS FOR LOW FLOW/HAZT
(PRESSURE/VACUUM AND SUBMERSION).
 3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLEMISHES, GATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DNPW-4.7-CS-01
 4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 5. FOR P/N 13711486 ONLY:
A SOLUTION OF 10:1 CONCENTRATION OF LUBEWELL S-60-TO WATER IS
TO BE APPLIED TO CONNECTOR SEALS. THIS IS TO AID CONNECTOR SEAL
TO CONNECTOR ASSEMBLY.
 6. PART NUMBER 13711486 MEASURES 148N MAX CONNECTOR INSERTION FORCE WHICH
EXCEEDS USCAR-2 REV. 04 REQUIREMENTS OF 75N MAX. PARTS WERE MEASURED
WITH CONNECTOR SEALS EXPOSED TO LUBEWELL S-60-TO ASSEMBLY AID.
 7. PART NUMBER 13711486: INSERTION FORCE OF PLR 1532662B MEASURES 130N
MAX WHICH EXCEEDS USCAR-2 REV. REQUIREMENT OF 60N MAX.
 8. MATERIAL RECYCLING CODE PER ISO 11469, 1.01X10.1. RAISED CHARACTERS
AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE, OPTIMAL CONSTRUCTION
NO MATERIAL RECYCLING CODE.

DRAWING NUMBER							
15326694							
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/P	
A1x3	5:1	2 OF 2	1 OF 2	R	31	-	

DIMENSIONAL RANGE (MM)		CHART	
FROM	TO		
> 0	> 20	> 30	> 100
		> 150	> 250
		> 300	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.15		±0.3	±0.5
		±0.6	±0.8
ANGULAR TOLERANCE ±2°			

<p>•APTIV•</p> <p>CONNECTION SYSTEMS</p> <p>WIRING, OR COPYRIGHT 1987 BY APTIV, ALL RIGHTS RESERVED.</p> <p>NO PARTING OR REUSE OF ANY OF APTIV'S AND COMPANY'S PATENTS, TRADE NAMES, OR INFORMATION OR INFORMATION CONTAINED HEREIN IS TO BE MADE WITHOUT THE WRITTEN CONSENT OF APTIV. ANY VIOLATION OF ANY CONTENT IS PROHIBITED, WITHOUT EXPRESS AUTHORIZATION. IS PROHIBITED.</p>	
<p>1. LINE SPEAK THROUGH FROM NUMBER 1 INDICATED THAT PHYSICAL PARTS ARE NOT AVAILABLE</p> <p>2. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.</p> <p>3. CONTACT APTIV SALES TO ACQUIRE AVAILABILITY OF PARTS.</p>	
<p>DRAWING</p>	
TITLE	DATE
ITEM 10091	01/28/00
	
<p>UNLESS OTHERWISE SPECIFIED</p> <p>THIS DRAWING IS IN ACCORDANCE WITH ASME Y14.5-1994 (MAY 1994 EDITION) FOR DIMENSIONING AND TOLERANCING PRACTICES (PERMITS THE USE OF UNLESS OTHERWISE SPECIFIED, TOLERANCING, AND DIMENSIONING PRACTICES). DEPARTURES ALLOWED FOR THE USE OF DIMENSIONS UNLESS OTHERWISE SPECIFIED.</p>	
<p>ALL DIMENSIONS ARE IN MILLIMETERS</p>	
<p>SEE DRAWING</p>	
<p>DRAWING NUMBER</p>	
<p>TAXI ASM CONN F 6T 280 SLD</p>	
<p>15326694</p>	
<p>SIZE SCALE FRAME OR 1 SHEET 1 OF 2</p> <p>A1x3 5:1 1"=1" 1"=1" 1"=1" 1"=1"</p>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15326642](#)