




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 106
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101



EXPLODED VIEW
SCALE 2:1



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLEMISHES, DATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EANP-4-3.CS.01.EN.
3. PART IS MANUFACTURED TO GEOMETRIC TOLERANCES. CENTERLINE
DIMENSIONS ARE FOR REFERENCE ONLY.
4. SEALING CODE 4 - DESIGN WILL MEET REQUIREMENTS OF SAE/USCAR-2
CONNECTOR SYSTEM ENVIRONMENTAL TEST FLOWCHART
(PRESSURE/VACUUM AND SUBMERSION).
5. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
6. FOR DIFFERENT PUNCH PATTERN CONFIGURATIONS (IF AVAILABLE) SEE SHEET 2
7. FOR ASSEMBLIES WITH 7MM CLIP SLOT SEE DRAWING 15514658

PART NO	REV	N/P	TYPE	MALE CONN	PLR	RETAINER	SEAL CBL	USCAR OPTION
35117277	01	AA	106	35117271	15514686	15514675	15514682	F
35117276	01	AA	105	35117270	15514686	15514675	15514682	E
35117275	01	AA	104	35117269	15514686	15514675	15514682	D
35117274	01	AA	103	35117268	15514686	15514675	15514682	C
35117273	01	AA	102	35117267	15514686	15514675	15514682	B
35117272	01	AB	101	35117266	15514686	15514675	15514682	A

N/A		PROCESS SENSITIVE DIMENSIONS			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED					
CHART					
>70 100	>100 150	>150 200	>200 250	>250 300	>300 400
LESS OTHERWISE SPECIFIED					
+0.4 +0.5 +0.6 +0.8 +1 +1.1 +1.2 +1.5 +2					
TOLERANCE					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[35117272](#)