




SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		NO MISSING SYMBOL NUMBER	
		TOTAL NO OF INSPECTIONS REQUIRED	
		6	
		LAST NO. USED	
		6	

DWG STATUS				REVISION HISTORY				AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG	ZONE								
20JN19	R	01	-	-		15543351, 13890301, 13890058 - WAS ON SHIT 1: 35366051 - RELEASED		443697	GDH	JAA	VRG		
28NO19	R	02	-	-		35366051 - UPDATED PART AVAILABILITY		550623	JAA	JAA	VRG		




NO BLOCKED CAVITIES

TYPE 202
SAME AS TYPE 201
EXCEPT AS SHOWN



BLOCKED CAVITIES (4 PLCS)


TYPE 203
SAME AS TYPE 201
EXCEPT AS SHOWN



Ø OF MALE BLADE

CONNECTOR SEAL - SEE CHART

POSITIVE LOCK REINFORCEMENT
SEE CHART
PRE-STAGE




CPA (PRE-STAGE)
SEE CHART


4 (24.43)

CONNECTOR - SEE CHART

STRAIN RELIEF - SEE CHART




CABLE SEAL - SEE CHART




BLOCKED CAVITIES (2 PLCS)

TYPE 201



BLOCKED CAVITIES (1 PLC)

TYPE 204
SAME AS TYPE 201
EXCEPT AS SHOWN



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- WHEN PARTS ARE SHIPPED THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINERS MUST BE SEALED TO AVOID FOREIGN MATTER.
- ASSEMBLY VALIDATED TO SAE/USCAR-2 REV 4 MAY 2004:

SEALING CODE 4 - CONNECTOR SYSTEM ENVIRONMENTAL TEST FLOWCHART (PRESSURE/VACUUM AND SUBMERSION).

ALSO CONFORMS TO:
SAE/USCAR-2 REV 6 FEB 2013 S3-ENVIRONMENTAL TEST SEQUENCE HIGH TEMP EXPOSURE; PV LEAK; SUBMERSION; HIGH PRESS. SPRAY.

TEMPERATURE CLASS 3

5.4.5 MISCELLANEOUS COMPONENT ENGAGE/DISENGAGE FORCE
PLR ENGAGE PRE-SET TO LOCK
WITHOUT TERMINALS: 69-78N
WITH TERMINALS: 57-73N
- THESE PARTS ARE NOT CONTROLLED FOR AUTOMATIC FEEDING.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER PER DPNP-4.7-CS-01.
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

DIMENSIONAL RANGE (MM)		TOLERANCE	
FROM	TO		
> 0	> 20	> 20	> 30
		30	70
		TOLERANCE	
		±0.15	±0.2
		±0.1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[35366051](#)