







VERSION	REF.	TITLE DESCRIZIONE	PART-NO	PART-REV	AMOUNT Q.TA'	MATER. AND COL. MATER. E COL.	LAYOUT OPEN CAVITY
A		32W FEMALE ASSEMBLY	33406557	02	1	--	ALL
	1	HOUSING FEMALE	33401494	02	1	PBTGF15 (Pocan trademark) / BLACK	--
	2	SEAL	33401547	01	1	SILICON RUBBER	--
A		32W FEMALE ASSEMBLY	33406618	00	1	--	ALL
	1	HOUSING FEMALE	33406619	02	1	PBTGF15 (Pocan trademark) / YELLOW	--
	2	SEAL	33401547	01	1	SILICON RUBBER	--
A		32W FEMALE ASSEMBLY	33295946	02	1	--	17way see table
	1	HOUSING FEMALE	33295931	02	1	PBTGF15 (Pocan trademark) / BLACK	
	2	SEAL	33401547	01	1	SILICON RUBBER	
A		32W FEMALE ASSEMBLY	33295960	02	1	--	23way see table
	1	HOUSING FEMALE	33295932	02	1	PBTGF15 (Pocan trademark) / BLACK	
	2	SEAL	33401547	01	1	SILICON RUBBER	
B		32W FEMALE ASSEMBLY	33406558	02	1	--	ALL
	1	HOUSING FEMALE	33401495	02	1	PBTGF15 (Pocan trademark) / GREY	--
	2	SEAL	33401547	01	1	SILICON RUBBER	--


VERSION	REF.	TITLE DESCRIZIONE	PART-NO	PART-REV	AMOUNT Q.TA'	LAYOUT OPEN CAVITY
A		32W ASSEMBLY KIT - BLACK	33406559	--	1	ALL
	1	32W FEMALE ASSEMBLY	33406557	02	1	--
	2	TPA FEMALE	33400990	02	1	--
B		32W ASSEMBLY KIT - GREY	33406560	--	1	ALL
	1	32W FEMALE ASSEMBLY	33406558	02	1	--
	2	TPA FEMALE	33400990	02	1	--

DRAWING NUMBER FSD 310275  
 NUMERO DISEGNO C  
 REVISION 09  
 SHEET 1/1  
 APPROVAL LEVEL 1/1

STRICTLY  
 CONFIDENTIAL



OPEN CAVITIES: 1,2,4,5,15,16,17,18,20,21,22,23,24,28,29,30,31



OPEN CAVITIES: 1,2,3,4,5,6,13,14,15,16,20,21,22,23,24,25,26,27,28,29,30,31,32

WIRE DIAMETER [mm]	SWS PART-NO	SWS COLOUR	PLUG PART-NO
1.2 - 1.6	15327913	RED	12198198 (delphi) 60993906 (fci)
1.7 - 2.1	15327918	GREY	
2.2 - 2.4	15339412	MAIZE	
1.1 - 2.1	10800583470 (Kostal)	WHITE	12010300 (DELPHI)
2.2 - 3	10800583410 (Kostal)	BLUE	
3.4 - 3.7	828985-1 (TE) or 10800583130 (Kostal)	GREEN ORANGE	



FEMALE TERMINAL UNSEALED	PART-NO		WIRE SIZE [mm²]
	Sn	Au	
CTS 1.5	15432237	15493005	0.35
	15432235	15493007	0.5 - 0.75
	15432233	15493009	1 - 1.5
DCK 2.8	60013611	--	0.35
	60013631	--	0.5 - 1
	60013641	--	1.5 - 2.5
	60013751	--	4

FEMALE TERMINAL SEALED	PART-NO		WIRE SIZE [mm²]
	Sn	Au	
CTS 1.5	15432208	15492999	0.35
	15432210	15493001	0.5 - 0.75
	15432212	15493003	1 - 1.5
DCK 2.8	60013711	60013714	0.35
	60013731	60013734	0.5 - 1
	60013741	60013744	1.5 - 2.5
	60013751	--	4


Male connect. version A	33406296	w/o CPA
	33406297	with CPA
Male connect. version B	33406299	w/o CPA
	33406300	with CPA

NOTES:  
 1 CAVITY NUMBER:  
 from 1 to 6 --> cavity 2.8x0.8  
 from 7 to 32 --> cavity 1.5 x0.8

TITLE DESCRIZIONE	PART-NO	PART-REV	MATER. AND COL. MATER. E COL.
TPA FEMALE	33400990	02	PBT GF15 / RED



SCALE 1:1



SCALE 1:1

--	14-11-2017	09	Added warpage note on dim. 25.2	F.G.	B.L.
16-17924	14-06-2016	08	Added SWS TE as option for wire size 4mm²	F.G.	B.L.
15-05641	20-10-2015	07	Added pinout 17way and 23way	F.G.	M.C.
15-15985	09-09-2015	06	Added version Yellow color	F.G.	M.C.
15-14942	31-07-2015	05	Added slot and link walls on the side openings of the connector. Replace DPNs' Female Assy and Kit	F.G.	M.C.
15-13944	14-05/2015	04	Added Material trademark for the female housing Replace DPNs Female Assy	DT	MP
	08/07/14	03	Added locking feature for cover	DT	MP
	13/05/14	02	Modified Tpa	DT	MP
	28/03/14	01	Updated dimensions; removed Preliminary	DT	MP

ECN-NO. NUMERO ECN	DATE DD/MM/YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY DISSEGNO	CHK. BY VERIFICA	APPR. BY APPROVATO
PRODUCT SPEC. SPEC. DI PRODOTTO	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	05/06/13	DT	MP
PACKAGING SPEC. SPEC. DI IMBALLAGGIO	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
APPLICATION SPEC. SPEC. DI APPLICAZIONE	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
COPYRIGHT	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
TOLERANCES TOLLERANZE	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
COUNTERPART N° CONTROPARTE N°	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
DO NOT SCALE DRAWING DISEGNO FUORI SCALA	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
DRAWN BY DISSEGNO	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
CHECKED BY CONTROLLATO	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP
APPROVED BY APPROVATO	DATE DATA	NAME NOME	TITLE DESCRIZIONE	32way Female sealed connector 32way sectioning connector	28/03/14	MP	MP

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

TORINO, ITALY

ISO PROJECTION PROIEZIONE ISO

DIMENSION IN MILLIMETERS DIMENSIONI IN MILLIMETRI

DWG SIZE FORMATO A2

SHEET 1/1

SCALE 2:1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33406557](#)