


3				2				1			
DWG STATUS				REVISION HISTORY				AUTH			
DATE	STG	REV	N/P/CHG	ZONE					DR	APVD	APVD
290C21	R	01			INITIAL RELEASE				P.BAL	M.LAG	M.LAG



SCALE 1:1

DWG. TYP		CUSTOMER PART DRAWING	
WEIGHT (GR)	SEE NOTE	DISTR CODE	D
VOLUME (CM ³)	---		
ROUTING			
UNLESS OTHERWISE SPECIFIED			
GENERAL TOLERANCES ACCORDING TO: SEE CHART			
GD&T ACCORDING TO: ISO 1101			
REFERENCE			
FIRST ANGLE PROJECTION			
DO NOT SCALE USE MATH DATA			

• APTIV •
CONNECTION SYSTEMS
Chennai, India
COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

DR	P.BALAJI	DATE	290C21
APVD1	LAGUETTE MAURICE		290C21
APVD2	LAGUETTE MAURICE		290C21
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

MATERIAL

SEE TABLE

DRAWING NAME


RECEPTACLE HOUSING 18 WAY
FOR MTS / MQS 0.64 TERMINAL

DRAWING NUMBER




13915990

SIZE	A1	SCALE	5:1	FRAME NO	1 OF 1	SHEET NO	1 OF 1	STG	R	REV	01	N/P	
------	----	-------	-----	----------	--------	----------	--------	-----	---	-----	----	-----	--


NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAGE TBD
2	FEMALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS TX -ENGINE VIBRATOR CLASS VX -SEALING CLASS EX
3	USER'S MANUAL: TBD
4	DELIVERY CONNECTOR WEIGHT :2.51g
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
△	MATERIAL CODE
△	TOOL CAVITY NUMBER
△	INDEX REPLCEMENT INDEX
△	PART CAVITY NUMBER
△	SUPPLIER LOGO
△	DATE INSERT



DIM TO CHECK		DIMENSIONAL RANGE (MM)											
FROM	TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	CHART	E1
1	1	0	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED													
□ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2			
ANGULAR TOLERANCE ±2°													



ASSOCIATED PARTS (FOR INFORMATION)			
DESCRIPTION	APTIV P/N	WIRE SECTION	DIAMETER OF WIRE SIZE
MATING PART	15345480	-	-
MQS 0.64 FEMALE SEALED TERMINAL	15341540	-	-



2	RECEPTACLE HOUSING 18 WAY	33343684	PBT GF20	BLACK
1	RECEPTACLE HOUSING 18 WAY	15345478	PBT GF20	BLACK
POS.	DESCRIPTION	APTIV PART NUMBER	MATERIAL	COLOR

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15345478](#)