







TYPE 102
SAME AS TYPE
EXCEPT AS SH
WITHOUT CP




TYPE 106
SAME AS TYPE 105
EXCEPT AS SHOWN
WITHOUT CPA





TYPE 110
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 114
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 118
SAME AS TYPE 101
EXCEPT AS SHOWN
WITHOUT CPA




ASSEMBLY VIEW
FOR REFERENCE ONLY




TYPE 103
SAME AS TYPE
EXCEPT AS SH
WITHOUT CR





TYPE 107
SAME AS TYPE 1
EXCEPT AS SHOWN




TYPE 111
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 115
SAME AS TYPE 101
EXCEPT AS SHOWN




PE 101




TYPE 104
SAME AS TYPE
EXCEPT AS SHOWN
WITHOUT CP




TYPE 108
SAME AS TYPE 107
EXCEPT AS SHOWN




TYPE 112
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 116
SAME AS TYPE 101
EXCEPT AS SHOWN



SECTION A - A



SECTION A - A

NO	N/P	TYPE	CONNECTOR	CONNECTOR SEAL	CABLE SEAL	STRAIN RELIEF	CPA	BLOCKED CAVITIES
01	01	10	3678.37	3678.95	3678.34	3678.33	33357583	
01	01	118	3678.37	3678.95	3678.34	35512834		1,2,8,11
01	AA	117	33177920	3678.95	3678.34	35067297	54884940	3,4,6,9,10,12
01	AB	116	33177920	3678.95	3678.34	35067295	54884940	4,6,10,12
01	01	115	3678.37	3678.95	3678.34	35027272	54884940	10,11,12
01	01	114	3678.37	3678.95	3678.34	35027272	54884940	3,6,7,9,10,12
01	AB	101	33177920	3678.95	3678.34	3678.33	54884940	
01	AB	101	33177919	3678.95	3678.34	3678.33	54884940	
01	AB	112	3678.37	3678.95	3678.34	33177919	54884940	7,12
01	AB	112	3678.37	3678.95	3678.34	33177919	54884940	5,10,11,12
01	AB	111	3678.37	3678.95	3678.34	33177919	54884940	5,10,11,12
01	AC	110	3678.37	3678.95	3678.34	33102623	59629682	5,6,10,11,12
01	AD	109	3678.37	3678.95	3678.34	35448740	59629682	1,2,3,5,6,8,9
01	AD	107	3678.37	3678.95	3678.34	35448740	59629682	8,9,12
01	AB	106	3678.37	3678.95	3678.34	35090719	59629682	1,8,9,12
01	AA	105	3678.37	3678.95	3678.34	35090719	59629682	1,8,9,12
01	AA	121	3678.37	3678.95	3678.34	38880740	54884940	2,3,4,6,12
01	AB	130	3678.37	3678.95	3678.34	38131308	54884940	
02	AB	104	3678.37	3678.95	3678.34	38204241		1,2,3,6,7,8
02	AB	101	3678.37	3678.95	3678.34	38204240		1,5,6,8,9
02	AB	102	3678.37	3678.95	3678.34			
02	AB	101	3678.37	3678.95	3678.34	3678.33		
NO	N/P	TYPE	CONNECTOR	CONNECTOR SEAL	CABLE SEAL	STRAIN RELIEF	CPA	BLOCKED CAVITIES

[illegible]

A LINE DRAWING INDICATES A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE NUMBER INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT MAIL SALES TO ASKURE AVAILABILITY OF PARTS.	
PART TYPE PART DRAWING	
STYLE	DISTR CODE
VOLUME (MM)	D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN CONFORMANCE WITH ANSI Y14.1-1994 AS AMENDED BY THE DIMENSIONING AND TOLERANCE INTERPRETATION (D & T) STANDARDS. SEPARATE PRACTICES OF DIMENSIONING MAY BE USED UNLESS OTHERWISE SPECIFIED BY DATA REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION 	DO NOT SCALE USE MATH DATA 

DELPH

CONNECTION SYSTEMS

PRINTING: DYNAMIC
COPYRIGHT 2007 DELPHI CORPORATION AND/OR ITS
ALL RIGHTS RESERVED

THIS DRAWING IS THE PROPERTY OF DELPHI
AND CONTAINS DELPHI OR OTHER IDENTICAL, UNPUBLISHED,
REGISTERED, OR PATENTED INFORMATION AND VITALITY
OF THIS DOCUMENT OR ITS RELATED AND MATTER
WILL BE COMMUNICATION OF THIS DOCUMENT
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED

DR
MPV
MPV3
MPV4
MPV5

G. LOPEZ G.
J. VILLAMAR
J. W. RICHARDSON

SUBSTANCES OF CONNECTION AND RECONNECTION
CONTENT REPT ARTV1 1094040

SEE CHART

DRAWING NAME
TAXI ASM CONN 12 005 1.2

DRAWING NUMBER
13678640

SIZE SCALE FRAME NO SHEET NO

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33178007](#)