

- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLENDES, GATE RESIDUE, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER ENP-41.3.CS.01-EN
 3. SEALING CODE 4 = DESIGN WILL MEET REQUIREMENTS OF SEA/ACAP-2
CONNECTOR SYSTEM ENVIRONMENTAL TEST FLOWCHART
(PRESSURE/VACUUM AND SUBMERSION).
 4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 5. FOR DIFFERENT PUNCH PATTERN CONFIGURATIONS (IF AVAILABLE) SEE SHEET 2.
 6. FOR ASSEMBLIES WITH 7MM CLIP SLOT SEE DRAWING 15513480.


35117262	01	AB	106	35117256	15513496	15513493	15513495	F	-----
35117261	01	AB	105	35117259	15513496	15513493	15513495	E	-----
35117260	01	AB	104	35117254	15513496	15513493	15513495	D	-----
35117259	01	AB	103	35117253	15513496	15513493	15513495	C	-----
35117258	01	AC	102	35117252	15513496	15513493	15513495	B	-----
35117257	01	AC	101	35117251	15513496	15513493	15513495	A	-----
PART NO	REV	N/P	TYPE	MALE CONN	PLR	RETAINDER	SEAL CBL	USCAR OPTION	

DIMENSIONAL RANGE (MM)								CHART	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
TO	20	30	70	100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
	+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2

THIRD ANGLE
PROJECTION

DO NOT
SCALE

USE MATH
DATA









DRAWING NUMBER

35117263

SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/A
A1x3	A1.1	1.05 2	1.05 2	0	04	

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35117257](#)