







TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 106
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 107
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 108
SAME AS TYPE 101
EXCEPT AS SHOWN






TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 1



EXPLODED VIEW
SCALE 2:1



- NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

- DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. SEALING CODE 3 - DESIGN WILL PASS SALT FOG AND IMMERSION TEST AFTER CONDITIONING AS SPECIFIED IN ESA-644 (WEATHER-PACK), ESA-710 (METRI-PACK), ESA-650 (UNDERHOOD MICRO-PACK), C-4006 (WORLD CONNECTOR), ETC WHEN MATED TO MATING PART OR EQUIVALENT

3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EANP_4-3-CS_01-EN
4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS

[illegible]

DIMENSIONAL RANGE (MM)		CHART	
FROM	TO		
> 0	> 20	> 30	> 70
> 20	> 30	> 70	> 100
> 30	> 70	> 100	> 150
> 70	> 100	> 150	> 200
> 100	> 150	> 200	> 250
> 150	> 200	> 250	> 300
> 200	> 250	> 300	> 400

TOLERANCE UNLESS OTHERWISE SPECIFIED

+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.5
-------	------	------	------	------	------	------	----	------

ANGULAR TOLERANCE ±2°

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT APPLIC SALES TO ASSURE AVAILABILITY OF PARTS.	
PART DRAWING	
DRW TYPE	
STYLE	
VOLUME NUMBER	DISTR CODE
D	
(UNLESS OTHERWISE SPECIFIED)	
THIS DOCUMENT IS IN ACCORDANCE WITH THE REQUIREMENTS OF THE FEDERAL ACQUISITION REGISTRATION STANDARD NO. 2512.700 (2512.150) (101-2240) REDUCTION, LABELING REQUIREMENTS.	
ALL DIMENSIONS ARE IN MILLIMETERS	
PN REFERENCE	1 3886481
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[35319763](#)