













SCALE 2:1



SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		TOTAL NO OF INSPECTIONS REQUIRED	23
LAST NO. USED		7	

DATE		AUTH		REV	
17AUG16	R 01	-	-	431992	M0 J5 J5
17JUL17	R 02	-	-	437240	J5M J5M J5M
23JUL18	R 03	-	-	440469	JAA JAA J5M
05JAN22	R 04	-	-	556179	EZJ JAA SV
17MAR22	R 05	-	-	556893	EZJ JAA SV

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS (INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, DATE VESTIGES) AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPMF-4.7-CS-01.
 - FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 - MAX TORQUE ALLOWABLE 6 N·M.

		N/A		PROCESS SENSITIVE DIMENSION						
				DIMENSIONS EMPLOYED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED						
DIMENSIONAL RANGE (MM)				CHART						
FROM	TO	> 0	> 20	> 30	> 100	>150	>200	>250	>300	
		TOLERANCE		LESS		TOLERANCE		SPECIFIED		
		±0.15		±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1
						ANGULAR TOLERANCE		±2°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33384584](#)