




DRAWING NUMBER							
1 357974 1							
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/P	
A1x3	2:1	2 OF 2	1 OF 1	R	27	-	



1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
 - DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT OF VIEW SHOWN, THE TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLENDS, DATE VENTS, AND SURFACE MARKS, DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER ENP-4.3.C.
 - THIS CONNECTOR MEETS SAE/USCAR-2 2013 REV 6 TERMINAL RETENTION (1-2013) AND 2013 REV 6.1 (2013) WITH A TERMINAL POSITION ASSURANCE (TPA) AND RETAINER APPLIED.
3. COVER END CAPS ARE NOT TO BE REMOVED FROM ASSEMBLIES.

35411627	01	-	109	33132250	3,4,6,7,8,9,11,16,17,19	15476350	15366672	35319845	15476349	15476349	-	-	-	
35411628	01	-	108	33132245	3,4,6,7,8,9,11,16,17,19	15476350	15366672	35319845	15476348	15476349	-	-	-	
35411552	01	AA	107	15476347	NONE	15476350	15366672	35319845	15476348	15476349	-	-	-	
35411629	01	-	106	13923409	3,4,6,7,8,9,11,16,17,19,20	15476350	13885426	35319845	15476348	15476349	-	-	13976571	
35411551	01	-	105	13885472	ALL	15476350	13885426	35319845	15476348	15476349	-	-	-	
35411550	01	AA	104	13885472	NONE	15476350	13885425	35319845	15476348	15476349	-	15476351	13976571	
35391377	01	AA	103	13672446	11,12,13,14,15,16	15476350	15366672	35319845	15476348	15476349	-	-	13976571	
35391349	01	AA	102	13570699	3,4,7,8,9,11,17,19	15476350	15366672	35319845	15476348	15476349	-	-	-	
35391378	01	AA	101	15476347	NONE	15476350	15366672	35319845	15476348	15476349	-	-	-	
35397976	01	-	110	35397975	11	15476350	15366672	15366622	15476348	15476349	-	-	-	
33132251	01	AC	109	33132250	3,4,6,7,8,9,11,16,17,19	15476350	15366672	15366622	15476348	15476349	-	-	-	
33132246	01	AC	108	33132245	3,4,6,7,8,9,11,16,17,19	15476350	15366672	15366622	15476348	15476349	-	-	-	
13976573	02	-	107	15476347	NONE	15476350	15366672	35319845	15476348	15476349	-	-	-	
13976574	02	AC	106	13923409	3,4,6,7,8,9,11,16,17,19,20	15476350	13885426	15366622	15476348	15476349	-	-	13976571	
13885475	05	-	105	13885473	NONE	15476350	13885426	35319845	15476348	15476349	-	15476351	13976571	
13885474	05	-	104	13885472	NONE	15476350	13885425	35319845	15476348	15476349	-	-	13976571	
13672447	02	AD	103	13672446	11,12,13,14,15,16	15476350	15366672	15366622	15476348	15476349	-	-	35391377	
13570698	02	AD	102	13570699	3,4,7,8,9,11,17,19	15476350	15366672	15366622	15476348	15476349	-	-	35411549	
15476346	04	N/P	101	15476347	NONE	15476350	15366672	15366622	15476348	15476349	-	-	35391378	
PART	NO	REV	N/P	TYPE	CONNECTOR	BLOCKED CAVITIES	ASSIST HANDLE	RETAINER	SEAL	SLIDE ASSIST RH	SLIDE ASSIST LH	WIRE DRESS COVER	COVER END CAP	REPLACED BY

DIMENSIONAL RANGE (MM)										CHART	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
		+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.6	
ANGULAR TOLERANCE ±2°											

1. TITLE	
LINE DRAWING THROUGH A PART NUMBER	
2. PURPOSE	
PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
3. COMMENTS	
PART NUMBER SALES TO HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT PARTS SALES TO ASSURE AVAILABILITY OF PARTS.	
4. DATE AND TIME	
PART DRAWING	
5. STYLE	
6. VOLUME (TEMP)	
7. DISTR CODE	
8. PART NUMBER	
9. PART NAME	
10. UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.3M-1994	
AND Y14.5M-1994 FOR DIMENSIONING AND TOLERANCING AND Y14.4M-1994 FOR	
TOLERANCING AND Y14.4M-1994 FOR TOLERANCING AND Y14.4M-1994 FOR TOLERANCING AND Y14.4M-1994 FOR TOLERANCING AND Y14.4M-1994 FOR TOLERANCING	
11. ALL DIMENSIONS ARE IN MILLIMETERS	
12. REFERENCE	
13. THIRD ANGLE PROJECTION	
14. DO NOT SCALE	
15. USE MATH DATA	
16. NX	

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35411552](#)