

REFERENCE STANDARD COMPONENTS:

- ASM COVER HIGH - 33268977
- ASM COVER FLAT - 33268985
- SECONDARY LOCK - 33260305

	TERMINAL	PART-NO.	CABLE CROSS SECTION (MM ²)	CABLE OUTER DIAMETER MIN-MAX (MM)
FEMALE TERMINAL MTS-B 0.64 SN	13580464	13580466	0.35	1.20 - 1.40
			0.75	1.40 - 1.60
FEMALE TERMINAL M05-CB 1.5 SN	10779820 (ITYCO PN 1241608-1)		0.75	1.70 - 1.90
			1.00	1.90 - 2.10
			1.50	2.20 - 2.40

* LINE DRAWING THROUGH A PART NUMBER INDICATES THAT IDENTICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT IDENTICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APRI SALES TO ASSURE AVAILABILITY OF PARTS.

R 0.1 MAX

R 0.2 MAX

90° SHARP CORNER TOLERANCE

DIMENSIONS (ORAL RANGE) (MM)

FROM	> 0	> 10	> 20	> 30	> 40	> 50	> 60	> 70	> 80	> 90	> 100	> 150	> 200	> 250	> 300	> 350	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	±1.5	±2	±3	±4	±5	±6	±8	±10

WZXM ZM
33281694-CUS01-501/26 Date: 04-dbr.-23 Time: 13:32:22
04042023,16:29,529pass,cus

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35516135](#)