






16
15
14
13
12
11
10
9
8
7
6
5
4
3
2
1
M
L
I
H
G
F
E
D
C
B
A
EUR CON 112 F23 POS




ASSOCIATED PARTS					
FEMALE TERMINALS	FCI REFERENCE	-	WIRE SIZE (mm ²)	TYPE	CENTERLINE SPACING
APEX MICRO FEMALE	SNAG PLATED	PCI 0001023	B	0.30 - 0.50	0.6X1.20
	SNAG PLATED	PCI 0001024	C	0.75 - 0.85	0.6X1.20
	SNAG PLATED	NOT AVAILABLE	D	1.00 - 1.25	0.6X1.20
DRESS COVER		F474000			
DESCRIPTION		FCI PART NUMBER			CUSTOMER PART NUMBER



- 1) USE 0.95/0.90 DIA ROUND NOSED POGO PIN.
- 2) USE 0.70/0.75 DIA TERMINAL REMOVAL PIN WITH NEEDLE POINT.

11	1	PUSH IN PLUG	PBT GF15	RED	.093	PC1000145
10	1	COVER	Dupont Zytel70G33HSIL	BLACK	12.04	F274000
9	1	RING SEAL	QSR	DARK RED	1.09	C844100
8	1	MATT SEAL	QSR	LT BLUE	5.43	C944100
7	1	LEVER	Dupont Zytel70G33HSIL	BLACK	7.67	S244100
6	1	SLIDER RIGHT HAND	..	..	2.96	S644100
5	1	SLIDER LEFT HAND	..	..	2.96	S544100
4	1	UNPLUGGED RETAINER	..	..	8.93	C944100
3	1	PLUGGED RETAINER	..	..	10.93	-
2	1	TPA	..	..	11.67	S744100
1	1	HOUSING	..	..	41.28	S444100
ITEM	QTY	DESCRIPTION	MATERIAL	COLOR	WEIGHT	FCI P/N
SPECIFICATION						
FCI : PRODUCT_SPEC:5 CUSTOMER : XX XX XX XXX						



- NOTES
1. ALL DIMENSIONS ARE REFERENCE ONLY
 2. 'D' GRIPS IN 3.0, 3.50 SPACING REQUIRE SPACIAL INSULATION CRIMP.
 3. THIS PRODUCT MUST MEET SPEC USCAR 2 REV4 CLASS 3
 4. TO MATE TO DELPHI HEADER PART NUMBER 12229168
 5. SEE DWG FILE PC10372642 FOR 58WAY ASSEMBLY.
 6. 'D' GRIPS IN 3.0, 3.50 SPACING REQUIRE SPECIAL INSULATION CRIMP.
 7. SEE PC10372642 FOR 58 WAY ASSEMBLY.
 8. 1.00, 1.25MM WIRE CAN ONLY BE USED IN 3.0, 3.5 COLUMN OF CAVITIES.

A 02 000		-		-		CHANGE DESCRIPTION	
PRODUCT SPEC	PACKAGING SPEC	APPLICATION SPEC	THIS DRAWING AND ALL OTHER INFORMATION CONTAINED THEREIN IS PROPRIETARY AND THE PROPERTY OF FCI. This drawing may not be copied, reproduced or disclosed to any third party without the expressed written permission of FCI. FCI April 1999				
TOLERANCES		MATERIAL :		SURFACE FINISH		CAD SYSTEM	
DIMENSIONS IN MILLIMETERS		COLOUR :		ECO Loc. Code		3RD ANGLE	
DO NOT MEASURE DRAWING		TOOL NO.		AN		DIM SIZE A1	
DATE		NAME		TITLE		DRAWING NUMBER	
CREATED BY		PROJECT		96 WAY ASSEMBLY		REV.	
CHECKED BY		PART NUMBER		154 WAY ASSEMBLY		STATE	
APPROVED BY		ESR NO.		CAT. NO.		PART NUMBER	
FILE NAME		PC10372645		DOCUMENT UNDER PDS CONTROL NO MODIFICATION ALLOWED OUTSIDE		F174000	
4		3		2		1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[F174000](#)