










FCI AUTOMOTIVE
MAY 26 2004
DIVISION

UNCONTROLLED
FCI MASTER COPY WHEN IN RED

PART NO.	GRIP SIZE	GRIP TYPE	B	C	"D" DIA	"E" DIA	H	J	K	M	N		
SA-1015-12	10	1	5.08	6.86	2.54	4.32	11.68	15.24	5.08	3.96	15"		
SA-1115-12	11	2	5.08	7.62	1.52	3.05	11.68	15.24	5.08	4.26	15"30"		
SA-1315-12	13	2	4.57	6.60	1.02	2.54	9.40	12.19	4.57	4.01	20"30"		
SA-1415-12	14	1	3.56	5.08	1.52	2.03	9.40	12.19	3.56	3.56	25"		
SA-1815-12	18	1	2.79	4.32	1.02	2.03	6.60	8.64	3.18	3.25	32"		

6673	5/19/04	B-1	-	REDRAWN IN PRO-E HAD DIMENTIONED IN METRIC ONLY 0.33/0.20 WAS 0.33	T. LANGER	S. SIAM	S. SIAM	
ECN NUMBER	DATE	W-D-Y	REVISION	ZONE	CHANGE DESCRIPTION	DRAWN BY	CHK. BY	APPR. BY
PRODUCT SPEC:		PACKAGING SPEC:		APPLICATION SPEC:		THIS DRAWING AND ALL OTHER INFORMATION CONTAINED HEREIN IS PROPRIETARY AND THE PROPERTY OF FCI. THIS DRAWING MAY NOT BE COPIED, REPRODUCED OR DISCLOSED TO ANY THIRD PARTY WITHOUT THE EXPRESSED WRITTEN PERMISSION OF FCI. APRIL 1999		
# 8-BULLET RECEPTACLE		N/A		N/A				
TOLERANCES: FRACTIONS DECIMALS		MATERIAL: N/A		SURFACE FINISH: N/A		CAP SYSTEM 3RD ANGLE PROJ. 1ST ANGLE DWG. STYLE		
CONTRACT NO. N/A		COLOR: N/A		C422 FULL HARD 0.404 ± 0.015 THICK		A FCI DRAWING NUMBER		
DO NOT SCALE DRAWING		TOOL NO. N/A		D088		ECO Ltr. Code: N/A		DIMENSION IN MILLIMETERS
DATE 1-24-77		NAME G EISENMANN		# 8 PIN RECEPTACLE (CONNECTOR TERMINAL)		SA-1815-12		A1 SHEET
CHECKED BY S. SIAM		APPROVED BY S. SIAM		ESP. NO. 6243		CAT. NO. FILE NAME		CONNECTOR_TERMINAL
SR NO. 1		REV. 1		REV. NO. 2		REV. DATE 5/19/04		SCALE: 4:1

FA02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[SA-1015-12](#) [SA-1815-12](#) [SA-1415-12](#)