




A

DO NOT SCALE

CTF  
IRS  
EN, C

12066266	D2		.0126 X 1.484	M1519447	12089008	C2		M1574447	20-22	.087-.051	121	.087	
			.0126 X 1.484	M1519447	12047504	C2		M1574447	TWO 18-20	.095-.081		.205	
12040658	B	OBSOLETE	.0126 X 1.484	U1519ABV					22-24	.082-.044		.085	
			.0126 X 1.484	M1519447	12034316	C2		M1574447	18-20	.095-.081		.120	
12020453	C2		.0126 X 1.484	M1519447					TWO 22	.073-.067	222	.140	
12010773	C	OBSOLETE	.0126 X 1.500	U1519AAS					22-24	.082-.044		.085	
8911904	C2		.0126 X 1.484	M1519447					12	.145-.139		.165	
6288108	G2		.0126 X 1.484	M1519447					14-16 OR TWO 18-20	.120-.101 .095-.081		.205	
2984794	F2		.0126 X 1.484	M1519447					18-20	.095-.081		.120	
PART NO	REV	STATUS	MAT'L SIZE	MAT'L SPEC	PART NO	REV	STATUS	MAT'L SPEC	GAGE	DIA	ID	C	
UNPLATED					TIN PLATED					CABLE			.015

[illegible]

<b>PIED / NIBGRAPH.</b> <b>MICROSTATION</b>		<b>FILE SPEC:</b> *****USER***** *****OPTION***** *****SYTIME*****	
<b>THIRD ANGLE PROJECTION</b> 		<b>ENGLISH</b> <b>DIMENSIONS ARE IN INCHES</b> <b>UNLESS OTHERWISE SPECIFIED.</b>	
<b>CODE NO.</b> 6900		<b>TOLERANCE UNLESS OTHERWISE SPECIFIED</b> DECIMALS TWO PLACES ± .01 THREE PLACES ± .005 ANGULAR ± 2°	
<b>Q.C.-1013</b>		<b>DR.</b> S. REIBOLD 10MR83	
<b>DWG. DATE</b> 09FE65	<b>SCALE</b> NONE	<b>CK.</b> D. BICE	<b>DATE</b> 28MR83
<b>REFERENCE NO.</b>		<b>APPR.</b>	<b>DATE</b>
<b>MATERIAL SPEC.</b>		<b>APPR.</b> R. D. KEARNS	<b>DATE</b> 05AP83
<b>SEE CHART</b>			
<b>NAME</b> TERM P/C BOW CNCT			
<b>PART NO.</b> 628 81 15	<b>SIZE</b> 		
<b>SHEET 1 OF 1</b>			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02984794](#)