




SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	32	
		25	



DWS STATUS				ZONE		REVISION HISTORY		AUTH	DR	AP/D
DATE	STG	REV	N/P	CHG						
19FE99	R	01	-	-			CLEARED REV COLUMN: 12191216-CANCELLED REV "D" & REVERTED BACK ORIGINAL DESIGN AT REV "A" - REVISION LEVEL ADVANCED	192332	LMM	661
22MR07	R	09	-	-			12191216 - UPDATED PDM ATTRIBUTES	400922	JBD	JVM
17FE09	R	10	-	-			12176461 - UPDATED MAT'L CALLOUT	407242	JAR	JAR






TYPE 101

#### NOTES




- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2,3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.
- (2,3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.






TYPE 102  
SAME AS TYPE 101  
EXCEPT AS SHOWN





TYPE 103  
SAME AS TYPE 101  
EXCEPT AS SHOWN



TYPE 104  
SAME AS TYPE 101  
EXCEPT AS SHOWN



TYPE 105  
SAME AS TYPE 101  
EXCEPT AS SHOWN



DIMENSIONAL RANGE (MM)		CHART
FROM	TO	
0	> 20	> 30
> 20	> 30	> 70
> 30	> 70	> 100
TOLERANCE UNLESS OTHERWISE SPECIFIED		
[+0.15] +0.2 -0.3 +0.4 -0.5		
ANGULAR TOLERANCE ±2°		

DWS TYPE		PART DRAWING	
STYLE		DISTR CODE	
VOLUME (QTY)		SEE CHART	
UNLESS OTHERWISE SPECIFIED		PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MDC	
THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WYOMING, OH	
DR J. M. SOVA	DATE 27AP94
AP/D1 J. M. SOVA	27AP94
AP/D2 J. M. SOVA	27AP94
AP/D3 GARY DETTER	29AP94
AP/D4	
AP/D5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
DRAWING NAME TAXI CONN F GT 150 SPL SAVER	
DRAWING NUMBER 12176518	
SIZE A0	SCALE 2:1
FRAME NO 1	SHEET NO 1
STG OF 1	REV 1
N/P	

PART	NO	REV	N/P	STATUS	TYPE	MATERIAL SPECIFICATION AND COLOR	MATING CAP ASM	VOLUME
12191216	B2	-	-	105	M3592012	PA66 HS IM GRA LT	12191217	5.084
12176461	C1	-	-	104	POLYAMIDE COMPOUND	BLACK	12176470	5.544
12176460	C1	-	-	103	R0071754	PA66 HS IM-BLK	12176469	5.544
12176459	C	-	-	102	R0071754	PA66 HS IM-BLK	12176468	5.544
12176458	C	-	-	101	R0071754	PA66 HS IM-BLK	12176467	5.544

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[12191216](#)